

XL³ S 630 - equipment for mounting modular devices and DPX³ on a rail



Selection chart p. 326 to 331

Pack	Cat.Nos	1-position rails
1	3 382 21	Used for mounting modular devices For 16-module enclosure
1	3 382 24	For 24-module enclosure
1	3 382 27	For 36-module enclosure
		3-position adjustable rails
		Used for mounting modular devices or DPX ³ 160/250 equipped with adaptors for rail
1	3 382 20	For 16-module enclosure
1	3 382 23	For 24-module enclosure
1	3 382 26	For 36-module enclosure
		Rail height spacer
1	3 382 40	Used to combine modular devices and DPX ³ 160/250 on the same rail
1	3 382 41	Used to combine modular devices and DRX on the same rail
1	3 382 42	Used to combine DRX and DPX ³ 160/250 on the same rail
		Adaptors for mounting DPX³ 160 and 250 on a rail
1	4 210 71	Used to mount DPX ³ on a rail
1	4 210 73	For DPX ³ 160 without side motor-driven handle
1	4 210 68	For DPX ³ 160 with e.l.c.b without side motor-driven handle
1	4 210 68	For all DPX ³ 160 devices with side motor-driven handle
1	4 210 72	For DPX ³ 250 without side motor-driven handle
1	4 210 74	For DPX ³ 250 with e.l.c.bs without side motor-driven handle
1	4 210 69	For all DPX ³ 250 devices with side motor-driven handle
		Window faceplates
		Fixed with 1/4 turn screws or screws
		Height 150 mm for modular devices
1	3 382 51	For 16-module enclosure
1	3 382 52	For 24-module enclosure
1	3 382 53	For 36-module enclosure
		Height 300 mm for DPX³ 160/250 and DPX-IS 250
1	3 382 71	For 16-module enclosure
1	3 382 72	For 24-module enclosure
1	3 382 73	For 36-module enclosure
		Height 400 mm for DPX³ 250 with e.l.c.b and terminal shields
1	3 382 81	For 16-module enclosure
1	3 382 82	For 24-module enclosure
1	3 382 83	For 36-module enclosure

XL³ S 630 - equipment for mounting DPX³ 125/160 HP and DRX 125 HP on a plate



Selection chart p. 326 to 331

Pack	Cat.Nos	Fixing plates for DPX ³ 125/160 HP and DRX 125 HP on side uprights
		Horizontal mounting
1	3 385 00 3 385 01	For 16-module enclosure
1	3 385 03 3 385 04	For 24-module enclosure
1	3 385 06 3 385 07	For 36-module enclosure
		Vertical mounting
1	3 385 21	For 16-module enclosure
1	3 385 23 3 385 24	For 24-module enclosure
1	3 385 26 3 385 27	For 36-module enclosure
		Faceplates for DPX³ 160/250 and DRX 125 HP/250 HP - horizontal mounting
		Fixed with 1/4 turn screws or screws
		DPX³ 160 - DRX 125 HP
		Height: 3P: 100 mm
		4P: 150 mm
1	3 383 53 3 383 54	For 24-module enclosure
1	3 383 56 3 383 57	For 36-module enclosure
		Window faceplates
		Fixed with 1/4 turn screws or screws
		Height 200 mm for DRX 125 HP and Vistop up to 160 A
1	3 382 61	For 16-module enclosure
1	3 382 62	For 24-module enclosure
1	3 382 63	For 36-module enclosure
		Faceplates for DPX³ 125/160 HP - horizontal mounting
		Fixed with 1/4 turn screws or screws
		Height: 250 mm
1	3 385 50 3 385 51	For 16-module enclosure
1	3 385 53 3 385 54	For 24-module enclosure
1	3 385 56 3 385 57	For 36-module enclosure
		Faceplates for DPX³ 125/160 HP - vertical mounting
		Fixed with 1/4 turn screws or screws
		Height: 250 mm
1	3 385 71	For 16-module enclosure
1	3 385 73 3 385 74	For 24-module enclosure
1	3 385 76 3 385 77	For 36-module enclosure