

# XL<sup>3</sup> S 4000

## equipment



Pack	Cat.Nos	Side or rear panels	Pack	Cat.Nos	Plinths for XL <sup>3</sup> S 630 and 4000 enclosures
		Fixed with a 1/4 turn screw			Height 100 mm
		<b>Height 2000 mm</b>			<b>Corner pieces for plinth</b>
		Width (mm)	1	3 382 00	Set of 4 corner pieces
1	3 380 60 <sup>1</sup>	200			<b>Finishing panel for plinth</b>
1	3 380 80	350			Set of 2 plates
1	3 380 61	400	1	3 382 01	For external cable sleeves width 324 mm
1	3 380 81	450	1	3 382 06	For enclosures depth 374 mm
1	3 380 62	600	1	3 382 02	For enclosures width 424 mm
1	3 380 63	800	1	3 382 03	For enclosures width / depth 574 mm
		<b>Height 2200 mm</b>	1	3 382 04	For enclosures width / depth 774 mm
1	3 380 70 <sup>1</sup>	200			<b>Plinths for corner enclosures</b>
1	3 380 90	350			Kits consisting of screws, corner pieces and finishing panel for plinth
1	3 380 71	400			Used in addition to the plinth supplied with the enclosure to double the height (200 mm)
1	3 380 91	450	1	3 382 10	For corner enclosure 400 x 400 mm
1	3 380 72	600	1	3 382 11	For corner enclosure 600 x 600 mm
1	3 380 73	800	1	3 382 12	For corner enclosure 800 x 800 mm
		<b>Faceplate supports</b>			<b>Joining kits</b>
1	3 381 56	Faceplate supports for enclosure height 2000 mm	1	3 379 50	For connecting two enclosures
1	3 381 58	Faceplate supports for enclosure height 2200 mm	1	3 379 49	Joining screws for XL <sup>3</sup> S 630 and 4000 enclosures
		<b>Crosspieces</b>			Joining plates for XL <sup>3</sup> S 630 and 4000 enclosures (to be used to strengthen joining)
		For fixing equipment in horizontal or vertical position			<b>Seal for IP 43 protection</b>
		To be equipped with fixing plates according to the required configuration	1	3 379 51	Supplied ready to use for XL <sup>3</sup> S 630 and 4000 enclosures
		<b>Side (depth) crosspieces</b>			<b>IP 30 finishing kits</b>
		Set of 4 crosspieces			Set of 2 finishing pieces
1	3 375 17	For enclosures depth 400 mm			Allow 1 horizontal kit and 1 vertical kit per enclosure
1	3 375 18	For enclosures depth 600 mm			<b>Finishing kits - vertical mounting</b>
1	3 375 19	For enclosures depth 600 mm			For enclosures with faceplate height (mm)
		<b>Central (width) crosspieces</b>	1	3 379 67	1800
		Set of 4 crosspieces	1	3 381 80	2000
1	3 375 14	For enclosures with 16 modules/row (width)			<b>Finishing kits - horizontal mounting</b>
1	3 375 15	For enclosures with 24 modules/row (width)			For enclosures with modules/row (width)
1	3 375 16	For enclosures with 36 modules/row (width)	1	3 379 72	16 modules
		<b>Side functional uprights</b>	1	3 379 73	24 modules
		For fixing equipment in horizontal or vertical position	1	3 379 74	36 modules
		Set of 2 uprights	1	3 379 71	For cable sleeves
1	3 381 55	For enclosures height 2000 mm			
1	3 381 57	For enclosures height 2200 mm			
		<b>Intermediate uprights</b>			
1	3 381 46	For enclosures height 2000 mm			
1	3 381 47	For enclosures height 2200 mm			
		<b>Internal cable sleeve kits</b>			
1	3 381 43	For XL <sup>3</sup> S 4000 enclosure height 2000 mm			
1	3 381 53	For XL <sup>3</sup> S 4000 enclosure height 2200 mm			

1: Used when joining 2 enclosures of different depths