

XL³ S 4000

universal accessories and mounting plates



3 395 40



3 395 60

Pack	Cat.Nos	Solid universal plates	
For 16-module enclosures			
		Height (mm)	
1	3 395 40	200	
1	3 395 41	300	
1	3 395 42	400	
1	3 395 43	600	
For 24-module enclosures			
1	3 395 44	200	
1	3 395 45	300	
1	3 395 46	400	
1	3 395 47	600	
For 36-module enclosures			
1	3 395 48	200	
1	3 395 49	300	
1	3 395 50	400	
1	3 395 51	600	

		Perforated universal plates	
For 16-module enclosures			
		Height (mm)	
1	3 395 60	200	
1	3 395 61	300	
1	3 395 62	400	
1	3 395 63	600	
For 24-module enclosures			
1	3 395 64	200	
1	3 395 65	300	
1	3 395 66	400	
1	3 395 67	600	
For 36-module enclosures			
1	3 395 68	200	
1	3 395 69	300	
1	3 395 70	400	
1	3 395 71	600	

		Universal support for cable sleeve
1	3 397 51	Vertical sloping support for cable sleeve

		Full-height solid mounting plates	
For installation in XL ³ S 4000 enclosures			
For enclosures			
		Height (mm)	Width (mm)
1	3 381 70	2000	600
1	3 381 71	2000	800
1	3 381 72	2200	600
1	3 381 73	2200	800

		Intermediate plate
1	3 381 74	For installation in XL ³ S 4000 enclosures For enclosures height 2200 mm Can be cut to height 2000 mm

XL³ S 4000

solid faceplates and fixing accessories for faceplates



3 395 88



3 395 85



3 390 80

		Full-height solid metal faceplates			
Fixed with 1/4 turn screws or screws					
		Faceplate total height (mm)	Faceplate usable height (mm)	Faceplate total width (mm)	Faceplate usable width (mm)
1	3 378 96	2000	1800	350	343
1	3 381 50	2200	2000	350	343

		Solid metal faceplates	
Fixed with 1/4 turn screws or screws			
Height 50 mm			
		For enclosures (modules)	Faceplate usable height (mm)
1	3 395 92	16	49
1	3 395 95	24	49
1	3 395 98	36	49
Height 100 mm			
1	3 395 93	16	99
1	3 395 96	24	99
1	3 395 99	36	99
Height 150 mm			
1	3 395 94	16	149
1	3 395 97	24	149
1	3 396 00	36	149
Height 200 mm			
1	3 395 80	16	199
1	3 395 84	24	199
1	3 395 88	36	199
Height 300 mm			
1	3 395 81	16	299
1	3 395 85	24	299
1	3 395 89	36	299
Height 400 mm			
1	3 395 82	16	399
1	3 395 86	24	399
1	3 395 90	36	399
Height 600 mm			
1	3 395 83	16	599
1	3 395 87	24	599
1	3 395 91	36	599

		Perforated plates for ventilation	
Fixed with 1/4 turn screws or screws			
Height 150 mm			
1	3 390 80	For 16-module enclosure	
1	3 390 81	For 24-module enclosure	
1	3 390 82	For 36-module enclosure	
Height 200 mm			
1	3 390 83	For 16-module enclosure	
1	3 390 84	For 24-module enclosure	
1	3 390 85	For 36-module enclosure	

		Fixing accessories for faceplates	
1	3 397 01	Set of 100 1/4 turn screws	
1	3 397 02	Set of 100 screws	