

Distribution enclosures XL³ 4000



Assembly consisting of:
 - Structural upright Cat.Nos 0 205 00
 - "Roof-base" Cat.Nos 0 205 03/06/09
 - Plinth Cat.Nos 0 205 17/18/19
 - Functional uprights Cat.Nos 0 205 24/27
 - Intermediate structural uprights Cat.No 0 205 20



0 205 12

Dimensions and installation principle **p. 383**
 Composition table **p. 382**

IP 30 - IK 07
 IP 55 - IK 10 with metal door or IK 08 with glass door and sealing kit for use when joining enclosures
 Consist of the combination of a "roof-base" assembly, structural uprights, functional uprights, rear and side panels RAL 7035, plinths RAL 7004
 Height 2000 or 2200 mm.
 Capacity 24 modules (enclosures width 725 or width 975 with internal cable sleeve), 36 modules (enclosures width 975)
 Usable faceplate height 1800 mm (1700 mm only if using the pivoting support frame) or 2000 mm

Pack	Cat.Nos	Enclosures and cable sleeves modular metal		
		Structural uprights Fit onto the "roof-base" assembly Take the side and rear panels Set of 4 uprights		
		Intermediate structural upright Fits on the structure of the enclosure "roof-base"		
		"Roof-base" for enclosure Fitted with cable entry plates Take the structural uprights		
		Depth (mm)	Width (mm)	
			external	usable
1	0 205 04	475	725	600
1	0 205 05	725	725	600
1	0 205 07	475	975	850
1	0 205 08	725	975	850
1	0 205 06	975	725	600
1	0 205 09	975	975	850
		"Roof-base" for cable sleeves Fitted with cable entry plates Take the structural uprights		
1	0 205 01	475	475	350
1	0 205 02	925	475	350
1	0 205 03	975	475	350
		Rear and side panels		
		Fixed with screws		
1	0 205 41 0 208 57	Width 475 mm		
1	0 205 42 0 208 58	Width 725 mm		
1	0 205 43 0 208 59	Width 975 mm		
		Finishing panels IP 30		
1	0 205 61 0 208 31	IP 30 width 475 mm		
1	0 205 62 0 208 32	IP 30 width 725 mm		
1	0 205 63 0 208 33	IP 30 width 975 mm		
		IP 55 strip IP 55 strip (for use when joining enclosures)		
		Plinths that can be placed side by side		
		Height (mm)	Width (mm)	Depth (mm)
1	0 205 11	100	475	475
1	0 205 14	100	725	475
1	0 205 15	100	725	725
1	0 205 17	100	975	475
1	0 205 18	100	975	725
1	0 205 19	100	975	975

Pack	Cat.Nos	Equipment		
		Functional uprights Set of 2 functional uprights For fixing mounting equipment (faceplate, rails...) Reduced functional uprights for enclosure depth 475 mm		
		For enclosure without internal cable sleeve		
		For enclosure with cable sleeve		
		Support frame for faceplates Fixed for enclosure width 725 mm or enclosure width 975 mm without internal cable sleeves		
		Fixed for enclosure width 975 mm with internal cable sleeves		
		Pivoting for enclosure width 725 mm		
		Pivoting for enclosure width 975 mm without internal cable sleeves		
		Pivoting for enclosure width 975 mm with internal cable sleeves		
		Spacer for functional uprights For fitting DPX on fixing devices or adjustable plates		
		Fixed crosspieces Fit onto structural uprights Fixed crosspieces are required for creating an internal cable sleeve		
		Set of 2 crosspieces length 350 mm		
		Set of 2 crosspieces length 600 mm		
		Set of 2 crosspieces length 850 mm		
		Adjustable crosspieces Fit onto structural uprights Specifically for busbar supports		
		Set of 2 crosspieces length 350 mm		
		Set of 2 crosspieces length 600 mm		
		Set of 2 crosspieces length 850 mm		
		Equipments for partial chassis Kit consisting of 4 fixing plates for reduced functional uprights Cat.No 0 205 12 To be used when assembling a double partial chassis		
		Set of 2 fixed crosspieces length 350 mm		
		Set of 2 fixed crosspieces length 600 mm		
		Front covers with hinges and lock For internal cable sleeve		
		For external cable sleeve		