

Plexo³

IP 65 weatherproof cabinets, multifunction sleeves and accessories



Technical characteristics **see opposite**

Self-extinguishing: resistance to glow wire 650°C. Allows to achieve assemblies conform to IEC 61 439 - 3
 Weatherproof cabinets - IP 65 - IK 09 - Class II
 Door and cabinet fully reversible. Removable chassis and faceplates from 2-row versions up
 2-position rail for modular products and moulded cases. Spacing between rails 150 mm
 Can be fitted with perforated plates and solid faceplates for mounting non-modular products
 Lockable door handle, sealable cover and faceplate. Shock-resistant polystyrene material
 Box colour light grey L750A, cover colour dark grey R746A. Supplied without terminal blocks

Pack	Cat.Nos	Cabinets 2 to 8 modules	
		Number of rows	Number of modules
6	6 019 32	1	2 (+1)
6	6 019 94	1	4
6	6 019 96	1	6
6	6 019 98	1	8

Pack	Cat.Nos	Cabinets 12 modules per row	
		Number of rows	
1	6 018 31	1	
1	6 018 32	2	
1	6 018 33	3	

Pack	Cat.Nos	Cabinets 18 modules per row	
		Number of rows	
1	6 018 35	1	
1	6 018 36	2	
1	6 018 37	3	
1	6 018 38	4	

Pack	Cat.Nos	Multifunction sleeves	
		Supplied with hinges connecting the cover to the back of the cabinet For use with 12 and 18-module cabinets using joining kit Cat.No 0 019 67 Can be fitted with control units and accessories: P17 16 A and 32 A sockets with standard fixing centres, flush-mounted IP 55 Plexo wiring accessories, Osmoz, modular rail at the back of the box	
1	0 019 17	Vertical For 2 rows cabinets	
1	0 019 18	For 3 rows cabinets	

Pack	Cat.Nos	Accessories	
5	0 019 71	Plexo adaptor For fixing Plexo flush-mounting wiring accessories, complete version (p. 791) on Plexo ³ cabinets (minimum 2 rows)	
		Installation supports for terminal blocks Set of 2 supports for mounting additional terminal blocks (p. 298) or empty supports for screw terminal blocks (p. 298) into Plexo ³ cabinets	
1	0 019 72	For 1 and 2 rows cabinets, 12 and 18 modules per row	
1	0 019 73	For 3 and 4 rows cabinets, 12 and 18 modules per row	
1	0 019 66	Key lock N° 850	
1	0 019 67	Joining kit Allows cables to be run horizontally or vertically between 2 cabinets or multifunction sleeves while maintaining IP 65 protection	
1	0 019 68	Sealing kit Set of 2 sealable screw caps for cover and 8 sealable supports for faceplate	
1	0 019 69	Fixing lugs Set of 4 wall mounting lugs for Plexo, Plexo ³ cabinets and P 17 combined units (p. 536)	
20	0 019 61	Blanking plates 5, separable into modules or 1/2 module Grey R746A	
1	0 019 55	Direct piercing end caps Pack consisting of 2 Ø32 mm ISO end caps, 5 Ø25 mm ISO end caps and 10 Ø20 mm ISO end caps	
1	0 019 56	Pack consisting of 100 Ø20 mm ISO end caps	
1	0 019 57	Pack consisting of 100 Ø25 mm ISO end caps	
1	0 019 58	Pack consisting of 100 Ø32 mm ISO end caps	
2	0 019 64	Plain faceplates For 12 modules cabinets	
2	0 019 65	For 18 modules cabinets	
2	0 019 62	Perforated plates Allow the DIN rail to be replaced with a LINA 25 plate when integrating non-modular products	
2	4 018 53	For 12 modules cabinets, Height 150 mm For 18 modules cabinets, Height 150 mm	
2	0 019 70	Hinges Set of 2 hinges connecting the back of the cabinet to the cover	

