

Equipment for Atlantic metal cabinets



0 363 17



Cabstop plate Cat.No 0 364 96 and mounting kit
Cat.No 0 364 98 on enclosure Cat.No 0 369 43

Cabinet and equipment selection chart p. 414-415
Technical characteristics p. 420-421

Pack	Cat.Nos	Metallic internal doors																																												
		<p>Metallic internal doors RAL 7035 For direct mounting in Atlantic metal and stainless steel cabinets IPXXB Reversible door with captiv hinge pins Double bar lock Can be equipped with other key barrels and metal rebate locks. Distance between cabinet door and internal door: 59 mm</p> <table border="1"> <thead> <tr> <th colspan="2">For cabinets (mm)</th> <th>Door dimensions (mm)</th> <th>Door usable dimensions (mm)</th> </tr> <tr> <th>Height x Width</th> <th>Height x Width</th> <th>Height x Width</th> <th>Height x Width</th> </tr> </thead> <tbody> <tr> <td>400 x 300</td> <td>334 x 248</td> <td>306 x 242</td> <td></td> </tr> <tr> <td>500 x 400</td> <td>434 x 348</td> <td>406 x 342</td> <td></td> </tr> <tr> <td>600 x 400</td> <td>534 x 348</td> <td>506 x 342</td> <td></td> </tr> <tr> <td>700 x 500</td> <td>634 x 448</td> <td>606 x 442</td> <td></td> </tr> <tr> <td>800 x 600</td> <td>734 x 548</td> <td>706 x 542</td> <td></td> </tr> <tr> <td>1000 x 600</td> <td>934 x 548</td> <td>906 x 542</td> <td></td> </tr> <tr> <td>1000 x 800</td> <td>934 x 748</td> <td>906 x 742</td> <td></td> </tr> <tr> <td>1200 x 600</td> <td>1134 x 548</td> <td>1106 x 542</td> <td></td> </tr> <tr> <td>1200 x 800</td> <td>1134 x 748</td> <td>1106 x 742</td> <td></td> </tr> </tbody> </table>	For cabinets (mm)		Door dimensions (mm)	Door usable dimensions (mm)	Height x Width	Height x Width	Height x Width	Height x Width	400 x 300	334 x 248	306 x 242		500 x 400	434 x 348	406 x 342		600 x 400	534 x 348	506 x 342		700 x 500	634 x 448	606 x 442		800 x 600	734 x 548	706 x 542		1000 x 600	934 x 548	906 x 542		1000 x 800	934 x 748	906 x 742		1200 x 600	1134 x 548	1106 x 542		1200 x 800	1134 x 748	1106 x 742	
For cabinets (mm)		Door dimensions (mm)	Door usable dimensions (mm)																																											
Height x Width	Height x Width	Height x Width	Height x Width																																											
400 x 300	334 x 248	306 x 242																																												
500 x 400	434 x 348	406 x 342																																												
600 x 400	534 x 348	506 x 342																																												
700 x 500	634 x 448	606 x 442																																												
800 x 600	734 x 548	706 x 542																																												
1000 x 600	934 x 548	906 x 542																																												
1000 x 800	934 x 748	906 x 742																																												
1200 x 600	1134 x 548	1106 x 542																																												
1200 x 800	1134 x 748	1106 x 742																																												
		Accessory																																												
1	0 363 69	Accessory for mounting insulating internal doors in Atlantic metal cabinets																																												

Pack	Cat.Nos	Cabstop open-work plate IP 55																				
		<p>Cable entries consisting of a cable clamp providing the mechanical grip, and elastomer areas for weatherproofing Can be pierced using the cable (no tool required) Fits the cable perfectly Replacement of a cable possible Fire retardant polypropylene RAL 7035 2 possibilities of mounting: - direct on cable entry of Atlantic or Marina cabinets - on flat surface with kit Cat.No 0 364 98 Supplied with: - locking caps for sealing a pierced entry providing IP 55 protection - cable release tool</p> <table border="1"> <thead> <tr> <th>Number of entries Ø5 to 14</th> <th>Number of entries Ø14 to 24</th> <th>Number of spare entries</th> <th>Direct mounting on cable entry of cabinet width (mm)</th> </tr> </thead> <tbody> <tr> <td>13</td> <td>1</td> <td>-</td> <td>300</td> </tr> <tr> <td>13</td> <td>1</td> <td>1</td> <td>400</td> </tr> <tr> <td>28</td> <td>2</td> <td>1</td> <td>500-1000</td> </tr> <tr> <td>28</td> <td>2</td> <td>2</td> <td>600-800-1200</td> </tr> </tbody> </table>	Number of entries Ø5 to 14	Number of entries Ø14 to 24	Number of spare entries	Direct mounting on cable entry of cabinet width (mm)	13	1	-	300	13	1	1	400	28	2	1	500-1000	28	2	2	600-800-1200
Number of entries Ø5 to 14	Number of entries Ø14 to 24	Number of spare entries	Direct mounting on cable entry of cabinet width (mm)																			
13	1	-	300																			
13	1	1	400																			
28	2	1	500-1000																			
28	2	2	600-800-1200																			
1	0 364 94	<p>Kit for mounting Cabstop plate on plain plate Enables mounting of 2 Cabstop plates: Cat.Nos 0 364 94 or 95 and 0 364 96 or 97 IP 55 maintained</p>																				
1	0 364 95																					
1	0 364 96																					
1	0 364 97																					
1	0 364 98																					