

MARINA CABINETS AND ENCLOSURES

Enclosures for all corrosive environments

Designed in fibreglass reinforced polyester, these enclosures are particularly suitable for corrosive environments: petrochemical, food processing industries and provide excellent UV resistance.



Marina enclosures

See p. 424

Marina cabinets

See p. 422

Discover the range

- Fiber glass reinforced polyester cabinets
- IP 66 - IK 10
- Class II (used to create totally isolated assemblies)
- 8 sizes of cabinets and 3 sizes of enclosures from 300 x 220 x 160 mm to 1800 x 800 x 400 mm
- Equipment fixed directly at the back of the cabinets thanks to a complete range of accessories

Marina cabinets

polyester - IP 66 - IK 10



0 362 56



0 362 76



Cabinet and equipment selection chart **p. 414-415**
Technical characteristics **p. 426 to 428**

IP 66 according to IEC EN 60529
LCIE n°60059283-560528
IK 10 according to IEC EN 62262 (EN 50102)
Class II (used to create totally isolated assemblies acc. to EN 60439-1 and assemblies for photovoltaic installations acc. to UTE C15-712-1)
Fiber glass reinforced polyester
Self-extinguishing 960°C acc. to IEC EN 60695-2-11
Adapted to corrosive environment and different weather conditions (detailed technical sheet available on e-catalogue)
Reversible door, opening 180°, (except Cat.No 0 362 50)
Stainless steel hinge pins (except Cat.No 0 362 50)
2 double bar lock (1 lock for Cat.No 0 362 50)
Direct fixing of equipment at bottom of cabinet (screws supplied)
Possible to fit a partial plate from 500 x 400 x 200 mm and/or rails on intermediate studs (except for Cat.No 0 362 50)
Optional depth adjustment from height 400 x width 300 mm with Cat.No 0 362 42
Can be equipped with Atlantic accessories

Pack	Cat.Nos	RAL 7035 cabinets	
		External dimensions (mm) Height x Width x Depth	Corresponding metal cabinets (mm) Height x Width x Depth
1	0 362 50	300 x 220 x 160	300 x 200 x 160
1	0 362 51	400 x 300 x 206	400 x 300 x 200
1	0 362 52	500 x 400 x 206	500 x 400 x 200
1	0 362 55	610 x 400 x 257	600 x 400 x 250
1	0 362 56	720 x 510 x 250	700 x 500 x 250
1	0 362 61	820 x 610 x 300	800 x 600 x 300
1	0 362 63	1020 x 810 x 300	1000 x 800 x 300
1	0 362 64	1220 x 810 x 300	1200 x 800 x 300

Pack	Cat.Nos	RAL 7035 cabinets with glass door	
		External dimensions (mm) Height x Width x Depth	Window dimensions (mm) Height x Width
1	0 362 71	400 x 300 x 206	235 x 145
1	0 362 72	500 x 400 x 206	335 x 245
1	0 362 75	610 x 400 x 257	463 x 245
1	0 362 76	720 x 510 x 250	570 x 272
1	0 362 81	820 x 610 x 300	672 x 372
1	0 362 83	1020 x 810 x 300	770 x 495
1	0 362 84	1220 x 810 x 300	970 x 495



Plastic industrial boxes
p. 807



Heat regulation for cabinets and enclosures
p. 440