

Equipment for Marina cabinets



Cabinet and equipment selection chart **p. 414-415**
 Technical characteristics **p. 426 to 428**

Pack	Cat.Nos	Plinths RAL 7035
1	0 362 91	Height 170 mm
1	0 362 92	Front and rear trap door
		Possibility to overlap 2 plinths
		For cabinets Cat.Nos 0 362 61/81
		For cabinets Cat.Nos 0 362 61/64/83/84
Pack	Cat.Nos	Roofs RAL 7035
1	0 362 93	For cabinets Cat.Nos 0 362 56/76
1	0 362 94	For cabinets Cat.Nos 0 362 61/81
1	0 362 95	For cabinets Cat.Nos 0 362 61/64/83/84
Pack	Cat.Nos	Fixing accessories
		IP 66 maintained
Pack	Cat.Nos	Wall mounting lugs
1	0 364 08	Set of 4, supplied with screws
		For cabinets height 300 mm
1	0 364 09	For cabinets height 400 and 1200 mm
		For 150 kg load
Pack	Cat.Nos	Rear with threaded rod
10	0 362 40	M8 for cabinets height \geq 400 mm
		Mounting at back of cabinets

Pack	Cat.Nos	Accessories
1	0 362 42	Depth adjustment kit for cabinets depth \geq 200 mm, for plate or uprights (p. 431)
10	0 394 49	Set of 4 lugs, supplied with screws
		Set of 2 supports for 45° rail slope
		Supplied with 4 M6 screws, nuts and washers
1	0 364 98	Kit for mounting Cabstop plate on plain plate
		Enables mounting of 2 Cabstop plates: Cat.Nos 0 364 94 or 95, and 0 364 96 or 97
1	0 362 44	IP 55 maintained
		Twin kit (horizontal or vertical) for cabinets \geq 500 mm height
		Comprising:
		- 1 frame for cable crossing and weather proofing
		- 2 linking pieces for fixing lugs (Cat.No 0 364 09 to be ordered separately)
1	0 365 13	Padlock adaptor stainless steel for Marina cabinets height \geq 400 mm additional to latches
		Takes 3 padlocks \varnothing 6 max.
Pack	Cat.Nos	Castors
1	0 464 83	Set of 4 pivoting casters
		Total permissible load on the 4 casters: 380 kg

Fixing accessories on ground
p. 431

IP 66 ventilation glands for cabinets
p. 441

