

# Heat regulation for cabinets and enclosures

## ventilators



0 348 17



0 348 52



exemple of plastic louvre mounted



0 348 54

Technical characteristics p. 442

Pack	Cat.Nos	Ventilator with metal louvre	Pack	Cat.Nos	Ventilators with plastic louvre (continued)
1	0 348 17	<p>IP 32 - IK 10 Ventilator is mounted on the outside of the enclosure or cabinet A second outlet can be installed to increase the flow rate and optimise discharge rates from the enclosure 230 V - 50/60 Hz</p> <p><b>30/160 m<sup>3</sup>/h :</b> 30 m<sup>3</sup> installed with filter 160 m<sup>3</sup> for free blow-out Supplied with a pair of metal louvres, a pair of anti-insect grilles and an internal finger-guard grille RAL 7035</p>	1	0 348 52	<p><b>240/450 m<sup>3</sup>/h</b> 240 m<sup>3</sup> installed with filter 260 m<sup>3</sup> with second louvre Cat.No 0 348 35 450 m<sup>3</sup> for free blow out Supplied with a pair of louvres 250 x 250 mm Media filter washable G3, acc. EN 779</p>
1	0 348 50	<p><b>Ventilators with plastic louvre</b></p> <p>IP 54 - IK 08 230 V - 50/60 Hz RAL 7035 Equipped with finger-guard grilles Reduced external dimensions (7 to 10 mm) Ventilator is mounted on the outside of the enclosure or cabinet Screw fixing on a panel width 1 to 4 mm A second outlet louvre can be installed to increase the flow rate and optimise discharge rates from the enclosure</p> <p><b>40/160 m<sup>3</sup>/h</b> 40 m<sup>3</sup> installed with filter 45 m<sup>3</sup> with second louvre Cat.No 0 348 34 160 m<sup>3</sup> for free blow out Supplied with a pair of louvres 150 x 150 mm equipped Electrostatic filter washable G3, acc. EN 779</p>	1	0 348 53	<p><b>400/900 m<sup>3</sup>/h</b> 400 m<sup>3</sup> installed with filter 450 m<sup>3</sup> with second louvre Cat.No 0 348 36 900 m<sup>3</sup> for free blow out Supplied with a pair of 325 x 325 mm Media filter washable G3, acc. EN 779</p>
1	0 348 51	<p><b>120/160 m<sup>3</sup>/h</b> 120 m<sup>3</sup> installed with filter 130 m<sup>3</sup> with second louvre Cat.No 0 348 35 160 m<sup>3</sup> for free blow out Supplied with a pair of louvres 250 x 250 mm Media filter washable G3, acc. EN 779</p>	1	0 348 54	<p><b>550/1200 m<sup>3</sup>/h</b> 550 m<sup>3</sup> installed with filter 620 m<sup>3</sup> with second louvre Cat.No 0 348 36 1200 m<sup>3</sup> for free blow out Supplied with a pair of louvres 325 x 325 mm Media filter washable G3, acc. EN 779</p>