

Plastic cable glands IP 68

ISO and PG



Technical characteristics p. 447

Anti-vibration mechanically tightened cable gland with neoprene weatherproof seal for IP 68 protection
Locking part consisting of flexible blades which exert strong pressure on the cable thus giving the product excellent tensile strength

Pack	Cat.Nos	Cable glands supplied with locking nut		
		Supplied with surface seal and locking nut (not mounted)		
		ISO		
		Conform to EN 62444		
			Clamping capacity	
		ISO	∅ Min. (mm)	∅ Max. (mm)
	Grey RAL 7001			
25	0 980 00	12	4	6
25	0 980 01	16	4	8
25	0 980 03	20	8	12
10	0 980 05	25	13	18
5	0 980 06	32	19	25
3	0 980 07	40	22	32
2	0 980 08	50	30	35
2	0 980 09	63	34	44
		PG		
		Conform to UTE C 68-300 and 68-311 guides recommendations		
			Clamping capacity	
		PG	∅ Min. (mm)	∅ Max. (mm)
25	0 980 20	7	3	8
25	0 980 21	9	4	8,5
25	0 980 22	11	5	10
25	0 980 23	13,5	8	12
20	0 980 24	16	10	14
10	0 980 25	21	12	18
5	0 980 26	29	18	25
3	0 980 27	36	22	32
2	0 980 28	42	30	38
2	0 980 29	48	34	44
		Grey RAL 7001 stopping plugs - ISO		
		Hexagonal with base ensuring the IP protection of the enclosure		
		Can be tightened using a flat screwdriver		
		Supplied with surface seal		
		Nuts to be ordered separately		
50	0 980 41	ISO 16		
50	0 980 43	ISO 20		
50	0 980 45	ISO 25		
25	0 980 46	ISO 32		
25	0 980 47	ISO 40		

Pack	Cat.Nos	Cable glands supplied without locking nut		
		Supplied with surface seal (not mounted)		
		Locking nuts to be ordered separately		
		ISO		
		Conform to EN 62444		
			Clamping capacity	
		ISO	∅ Min. (mm)	∅ Max. (mm)
	Black RAL 9011			
	Grey RAL 7035			
50	3 815 58	12	4	6
50	3 815 59	16	4	8
50	3 815 60	20	8	12
35	3 815 61	25	13	18
20	3 815 62	32	19	25
10	3 815 63	40	22	32
5	3 815 64	50	30	35
5	3 815 65	63	34	44
		PG		
		Conform to UTE C 68-300 and 68-311 guides recommendations		
			Clamping capacity	
		ISO	∅ Min. (mm)	∅ Max. (mm)
	Black RAL 9011			
	Grey RAL 7035			
50	3 815 66	7	3	8
50	3 815 67	9	5	8,5
50	3 815 68	11	6	10
50	3 815 69	13,5	8	12
50	3 815 70	16	10	14
35	3 815 71	21	12	18
20	3 815 72	29	18	25
10	3 815 73	36	22	32
5	3 815 74	42	30	38
5	3 815 75	48	34	44
		Plastic locking nuts		
		For hexagonal plastic cable glands supplied without locking nut, with base to protect the sur-face of the enclosure during tightening		
		ISO		
		Conform to EN 62444		
			Clamping capacity	
		ISO	∅ Min. (mm)	∅ Max. (mm)
	Black RAL 9011			
	Grey RAL 7035			
50	3 866 71	12	4	6
50	3 866 72	16	4	8
50	3 866 73	20	8	12
50	3 866 74	25	13	18
200	3 866 75	32	19	25
100	3 866 76	40	22	32
10	3 866 77	50	30	35
10	3 866 78	63	34	44
		PG		
		Conform to UTE C 68-300 and 68-311 guides recommendations		
			Clamping capacity	
		ISO	∅ Min. (mm)	∅ Max. (mm)
	Black RAL 9011			
	Grey RAL 7035			
50	3 866 61	7	3	8
50	3 866 62	9	5	8,5
50	3 866 63	11	6	10
50	3 866 64	13,5	8	12
50	3 866 65	16	10	14
50	3 866 66	21	12	18
25	3 866 67	29	18	25
10	3 866 68	36	22	32
10	3 866 69	42	30	38
10	3 866 70	48	34	44