

# Colring™ equipment cable ties



0 320 37 blister packing



0 320 42 blister packing



0 320 61/14/31/19/20/49



0 318 24



0 318 04

**Technical characteristics p. 452**

For series assembly of electrical cables  
With self blocking head and internal teeth  
Conform to IEC/EN 62275 (NFC 68-146)

**Colring colourless cable ties**

Pack	Cat.Nos	Blister packing 100 pcs			
		Width (mm)	Flat length (mm)	Ø grip capacity (mm)	
10000	0 320 30 <sup>1</sup>	2.4	95	18	1.6
10000	0 320 31	2.4	140	33	1.6
6000	0 320 32	2.4	180	46	1.6
4000	0 320 37	3.5	140	33	1.6
4000	0 320 38	3.5	180	46	1.6
2000	0 320 39	3.5	280	77	1.6
2000	0 320 40	3.5	360	102	1.6
4000	0 320 42	4.6	180	46	1.6
2000	0 320 43	4.6	280	77	1.6
2000	0 320 44	4.6	360	102	1.6
1000	0 320 47 <sup>3</sup>	7.6	180	42	4.8
100	0 320 49 <sup>3</sup>	7.6	360	98	4.8
100	0 320 50 <sup>3</sup>	7.6	720	218	4.8
1000	0 320 45 <sup>2</sup>	7.6	550	147	15
1000	0 320 46 <sup>2</sup>	9	760	208	12
500	0 320 48 <sup>2</sup>	9	810	223	12
500	0 320 51 <sup>4</sup>	12.6	1030	285	15
<b>Sachet packing 100 pcs</b>					
8000	0 318 20	2.4	95	20	3
4000	0 318 21	2.4	140	32	3
4000	0 318 22	2.4	180	50	4
4000	0 318 23	3.5	140	31	3
4000	0 318 24	3.5	180	44	4
4000	0 318 25	3.5	280	75	7
3000	0 318 26	3.5	360	96	7
4000	0 318 27	4.6	180	45	4
3000	0 318 28	4.6	280	70	7
2500	0 318 29	4.6	360	96	7
100	0 318 33	4.6	430	115	7
1500	0 318 34	7.6	290	73	8
1000	0 318 31	7.6	360	90	8
100	0 318 35	7.6	550	147	15
100	0 318 32 <sup>1</sup>	7.6	720	218	4.8
100	0 318 36	9	710	208	12

**Identification colourless cable ties**

Pack	Cat.Nos	Sachet packing 100 pcs			
		Width (mm)	Flat length (mm)	Ø grip capacity (mm)	
3000	0 320 61 <sup>1</sup>	2.4	95	18	1.6
2500	0 320 63 <sup>1</sup>	4.6	180	46	9.5

**Colring black cable ties**

High temperature  
UV protected

Pack	Cat.Nos	Blister packing 100 pcs			
		Width (mm)	Flat length (mm)	Ø grip capacity (mm)	
1000	0 320 12 <sup>1</sup>	2.4	95	18	1.6
1000	0 320 13	2.4	140	33	1.6
1000	0 320 14	2.4	180	46	1.6
1000	0 320 15	3.5	140	33	1.6
1000	0 320 18	3.5	180	46	1.6
2000	0 320 19	3.5	280	77	1.6
2000	0 320 20	3.5	360	102	1.6
1000	0 320 22	4.6	180	46	1.6
2000	0 320 23	4.6	280	77	1.6
2000	0 320 24	4.6	360	102	1.6
2000	0 320 29 <sup>3</sup>	7.6	360	98	4.8
100	0 320 25 <sup>2</sup>	7.6	550	147	15
100	0 320 26 <sup>2</sup>	9	760	208	12
500	0 320 27 <sup>2</sup>	9	810	223	12
500	0 320 28 <sup>4</sup>	12.6	1030	285	15
<b>Sachet packing 100 pcs</b>					
8000	0 318 00	2.4	95	20	3
4000	0 318 01	2.4	140	32	3
4000	0 318 02	2.4	180	50	4
4000	0 318 03	3.5	140	31	3
4000	0 318 04	3.5	180	44	4
4000	0 318 05	3.5	280	75	7
3000	0 318 06	3.5	360	96	7
4000	0 318 07	4.6	180	45	4
3000	0 318 08	4.6	280	70	7
2500	0 318 09	4.6	360	96	7
100	0 318 13	4.6	430	115	7
1500	0 318 14	7.6	290	73	8
1000	0 318 11	7.6	360	90	8
100	0 318 15	7.6	550	147	15
100	0 318 12 <sup>1</sup>	7.6	720	218	4.8
1000	0 318 16	9	710	208	12

1: Non orientated head  
2: Sachet packing 100 pcs  
3: Non orientated head and sachet packing 100 pcs  
4: Sachet packing 50 pcs

