Lina 25™ cable ducting






Manually separable trunking


Side wall fingers can be cut using the Lina 25 cutter tool
Cat.No 0 367 10

Technical characteristics **p. 481**

Pack	Cat.Nos	Lina 25 ducting
		PVC Blue 2525 according to AFNOR NF X08-002 Conform to EN 50085-2-3 6.5 mm wide fingers with a 6 mm spacing Accepts up to 6 mm² without breaking side wall fingers Two pre-scored lines allow removal of fingers Bump on side wall fingers help cabling Rounded fingers prevent injury during cabling Conform to EN 50085 parts 2 and 3 Plastic cable ducting (base + cover) Side perforations at intervals of 12.5 mm Length: 2 m
		Width x height (mm)
60[1]	0 362 00	25 x 25
56[1]	0 362 01	25 x 40
56[1]	0 362 02	25 x 60
40[1]	0 362 03	25 x 80
56[1]	0 362 05	40 x 25
48[1]	0 362 06	40 x 40
48[1]	0 362 07	40 x 60
40[1]	0 362 08	40 x 80
32[1]	0 362 11	60 x 40
32[1]	0 362 12	60 x 60
32[1]	0 362 13	60 x 80
24[1]	0 362 16	80 x 60
24[1]	0 362 17	80 x 80
16[1]	0 362 25	120 x 80
		Lina 25 cutter tool
1	0 367 10	For a straight break of side wall fingers
		Sleeving
		Braided sleeving Black polyester Supplied in 50 m roll in dispenser box with an indicator 3 m before end
		Ø of roll / Ø variations
1	0 366 38	20 mm / 10 to 30 mm
1	0 366 39	30 mm / 18 to 54 mm
		Spiral sleeving Colourless
25	6 361 78	Ø12 mm
25	6 361 83	Ø22 mm
		Black felt-tip pen
10	0 395 98	Black felt-tip pen indelible for marking

1: Number of metres in pack

Pack	Cat.Nos	Linafix isulating fixing accessories
		Material: polyamide 6/6 Enable fixing cable ducting on any support by 1/4 turn
100	0 366 40	On rails ⊏⊐, ⊐⊏ 15 mm depth 1/4 turn
20	0 366 41	On Lina 25 perforated plates Clip-on 1/4 turn
20	0 366 42	On door Fits under control and signalling auxiliaries Osmoz (Ø22)
10	0 366 43	On Lina 25 uprights Double adjustment to enable alignment with the perforations at the bottom of cable ducting Can be used to fix vertical or horizontal ducting (possible reinforcement with rail ⊐⊏, 15 mm depth) To be clipped on
100	0 366 46	On plain plates plastic rivet length 12 mm for solid plates up to 30 / 10th Drilling Ø: 5.5 to 6 mm
500	0 366 44	On plain plates, Lina 12.5 and perforated plates, Lina 25 for cabinets Reinforced plastic rivet Ø6 mm Drilling Ø: 6.5 mm
100	0 347 45	Screw caps H 4.8 x 16 mm self-drilling, self-tapping for Ø3.3 mm
200	0 347 50	Screw cover, for isolating screws head Cat.No 0 347 45 inside the trunking
50	0 367 01	Cable retainer To clip-on the fingers