

# Osmoz control and signalling units: non-illuminated heads



Technical characteristics p. 487  
Dimensions p. 488-489

Supplied with a fixing ring  
IP 69, IP 69K except Cat.Nos 0 238 11/12/13 - IP 67 and Cat.Nos 0 239 80/82 - IP 66  
Conform to IEC 60947-5-1

Pack	Cat.Nos	Spring return
		<b>Flush</b>
10	0 238 00	○ White
10	0 238 01	● Red
10	0 238 02	● Green
10	0 238 03	● Blue
10	0 238 04	● Yellow
10	0 238 06	● Black
1	0 238 08	● Red engraved "O"
1	0 238 09	● Green engraved "I"
		<b>Flush with shroud - IP 67</b>
5	0 238 11	● Red
5	0 238 12	● Green
5	0 238 13	● Black
		<b>Projecting</b>
5	0 238 21	● Red
1	0 238 22	● Green
5	0 238 26	● Black
		<b>Mushroom head Ø40</b>
10	0 238 34	● Red
10	0 238 35	● Green
10	0 238 36	● Black
1	0 238 37	● Yellow
		<b>Twin touch - IP66</b>
5	0 239 80	Red engraved "O", green engraved "I"
5	0 239 82	Flush/Flush - Green/Red Flush/Projecting - Green/Red

Pack	Cat.Nos	Stay-put mushroom heads
		<b>Push-pull emergency stop</b>
10	0 238 72	● Red - Ø40
1	0 238 76	● Black - Ø40
		<b>Push-pull ISO 13850 emergency stop</b>
10	0 238 74	● Red - Ø40
1	0 238 94	● Red - Ø54
		With flag indicator "O - I"
5	0 238 95	● Red - Ø54
		With flag indicator "STOP - I"
		<b>Push-turn emergency stop</b>
10	0 238 80	● Red - Ø32
1	0 238 81	● Black - Ø32
10	0 238 82	● Red - Ø40
1	0 238 83	● Black - Ø40
		<b>Push-turn ISO 13850 emergency stop</b>
10	0 238 85	● Red - Ø40
		<b>Emergency stop with key</b>
10	0 238 91	● Red - Ø40
		<b>ISO 13850 emergency stop with key</b>
1	0 238 92	● Red - Ø40

Pack	Cat.Nos	Selector switches	Positions
		<b>With standard handle</b>	
1	0 239 02	● Green	 2 stay-put positions - 45°
10	0 239 03	● Black	
1	0 239 04	● Grey	
1	0 239 09	● Black	 2 positions with spring-return - 45°
10	0 239 15	● Black	 2 stay-put positions - 90°
1	0 239 21	● Red	 3 stay-put positions - 45°
1	0 239 22	● Green	
10	0 239 23	● Black	
1	0 239 24	● Grey	
1	0 239 26	● Black	 3 positions with spring-return from left to 0 - 45°
1	0 239 27	● Black	 3 positions with spring-return from right to 0 - 45°
5	0 239 28	● Black	 3 positions with spring-return to 0 - 45°
1	0 239 29	● Black	 3 stay-put positions - 90°

Weatherproof cabinets,  
p. 416

