

Osmoz control and signalling units: block sub-assemblies



Osmoz control and signalling units: electrical blocks



0 229 61



0 229 76



0 229 78



0 229 01



0 229 02



0 229 42



0 230 14



0 229 60



0 229 64



0 229 68

Technical characteristics p. 487
Dimensions p. 488-489

Clip and screw electrical blocks assembled
Conform to IEC 60947-5-1

Pack	Cat.Nos	For non-illuminated heads
		Screw terminals
10	0 229 61	NC + 1 position clip
10	0 229 62	NO + 1 position clip
5	0 229 65	NO/NC + 3 position clip
5	0 229 66	2 x NO/NC + 3 position clip
1	0 229 71	NC + 3 position clip
1	0 229 72	NO + 3 position clip
10	0 229 73	2 NC + 3 position clip
10	0 229 74	2 NO + 3 position clip
10	0 229 76	NO + NC + 3 position clip
1	0 229 77	2 NO + NC + 3 position clip
1	0 229 78	NO + 2 NC + 3 position clip

Pack	Cat.Nos	For illuminated heads
		Screw terminals
		With 3 position clip
1	0 229 80	○ White - 12-24 V~/= - 2 NO/NC
1	0 229 81	● Red - 12-24 V~/= - 2 NO/NC
1	0 229 82	● Green - 12-24 V~/= - 2 NO/NC
5	0 230 00	○ White - 12-24 V~/= - NO
5	0 230 01	● Red - 12-24 V~/= - NO
5	0 230 02	● Green - 12-24 V~/= - NO
1	0 230 03	○ White - 12-24 V~/= - NO + NC
1	0 230 04	● Red - 12-24 V~/= - NO + NC
1	0 230 05	● Green - 12-24 V~/= - NO + NC
5	0 230 06	○ White - 12-24 V~/= - 2 NO
5	0 230 07	● Red - 12-24 V~/= - 2 NO
5	0 230 08	● Green - 12-24 V~/= - 2 NO
1	0 229 90	○ White - 230 V~ - 2 NO/NC
1	0 229 91	● Red - 230 V~ - 2 NO/NC
1	0 229 92	● Green - 230 V~ - 2 NO/NC
5	0 230 10	○ White - 230 V~ - NO
5	0 230 11	● Red - 230 V~ - NO
5	0 230 12	● Green - 230 V~ - NO
1	0 230 13	○ White - 230 V~ - NO + NC
1	0 230 14	● Red - 230 V~ - NO + NC
1	0 230 15	● Green - 230 V~ - NO + NC
5	0 230 16	○ White - 230 V~ - 2 NO
5	0 230 17	● Red - 230 V~ - 2 NO
5	0 230 18	● Green - 230 V~ - 2 NO

Technical characteristics p. 487
Dimensions p. 488-489

IP 20
Conform to IEC 60947-5-1

Pack	Cat.Nos	For non-illuminated heads
		Contact blocks
		Screw terminals
20	0 229 01	NC
20	0 229 02	NO
10	0 229 03	NO/NC
		For illuminated heads
		Screw terminals
5	0 229 10	○ White - 12-24 V~/=
5	0 229 11	● Red - 12-24 V~/=
5	0 229 12	● Green - 12-24 V~/=
5	0 229 13	● Blue - 12-24 V~/=
5	0 229 14	● Yellow - 12-24 V~/=
1	0 229 20	○ White - 48 V~/=
1	0 229 21	● Red - 48 V~/=
1	0 229 22	● Green - 48 V~/=
1	0 229 23	● Blue - 48 V~/=
1	0 229 24	● Yellow - 48 V~/=
5	0 229 40	○ White - 230 V~
5	0 229 41	● Red - 230 V~
5	0 229 42	● Green - 230 V~
5	0 229 43	● Blue - 230 V~
5	0 229 44	● Yellow - 230 V~
		Clips
		Mounting (p. 487)
20	0 229 60	1 position
20	0 229 64	3 positions
10	0 229 68	5 positions