

## Osmoz control and signalling units control stations to be equipped



Technical characteristics **p. 487**  
Dimensions **p. 488-489**

Empty control stations to be equipped with:  
- illuminated or non-illuminated heads (p. 482 to 484)  
- specific blocks for control stations

### Control stations (to be equipped) IP 66 - IK 07

Pack	Cat.Nos	
1	0 242 00	Possibility to mount 3 electrical blocks per hole
1	0 242 01	1 hole - grey
1	0 242 02	1 hole - yellow cover
1	0 242 03	2 holes - grey
1	0 242 04	3 holes - grey
1	0 242 05	4 holes - grey
1	0 242 05	5 holes - grey

### Specific blocks

#### Contact block mounted on control station base

#### Screw terminals

10	0 242 41	NC
10	0 242 42	NO

#### Illuminated LED blocks

1	0 242 50	○ White - 12-24 V~/=
1	0 242 51	● Red - 12-24 V~/=
1	0 242 52	● Green - 12-24 V~/=
1	0 242 53	● Blue - 12-24 V~/=
1	0 242 54	● Yellow - 12-24 V~/=
1	0 242 70	○ White - 230 V~
1	0 242 71	● Red - 230 V~
1	0 242 72	● Green - 230 V~
1	0 242 74	● Blue - 230 V~
1	0 242 73	● Yellow - 230 V~

## Osmoz control and signalling units accessories



### Mounting accessories

Pack	Cat.Nos	
		<b>IP 67 shroud</b>
		Reinforced degree of protection: IP 67
		For spring return buttons
5	0 241 90	○ Transparent
5	0 241 91	● Red
5	0 241 92	● Green
5	0 241 93	● Black
1	0 241 96	○ Transparent for twin touch flush/projecting
1	0 241 81	Yellow - standard padlockable guard for mushroom head
		<b>Miscellaneous</b>
1	0 241 88	Padlockable shroud
10	0 241 87	Blanking plug - black
1	0 241 85	Fixing tool

### Legend plates

		To mount on frame
		<b>Without engraving</b>
10	0 243 02	○ Alu - standard model
10	0 243 03	● Black - standard model
10	0 243 07	○ Alu - large model
10	0 243 08	● Black - large model
		<b>With engraving</b>
		○ Alu - standard model
10	0 243 30	"O I"
10	0 243 32	"I O II"
10	0 243 43	"MANU - AUTO"
10	0 243 44	"MANU - O - AUTO"
10	0 243 51	"START"

### Round legend plate for mushroom head

		● Yellow
10	0 241 76	ø60 "EMERGENCY STOP" + symbol
10	0 241 79	ø80 "EMERGENCY STOP" + symbol

### Frames

		Supplied without legend plate
		<b>Without engraving</b>
10	0 243 15	Round - standard model
10	0 243 16	Round - large model
10	0 243 18	Square - standard model
10	0 243 19	Round - standard model for twin touch