

Cam switches insulating box



Technical characteristics p. 491 to 493
 Dimensions p. 491

For selecting and changing the status of the circuits into which it is integrated
 For viewing the state of equipment according to the position of the selector lever
 Boxed device, class II. Contacts with positive opening and double breaking of poles
 Presentation: black or grey/black selector lever, faceplate with marking
 Conform to standards IEC EN 60947-3
 IP 65 for 76 x 76 and 96 x 120 mm boxes. IP 55 for 135 x 170 mm boxes

Pack	Cat.Nos	Function: on/off switch				
		76 x 76 mm box				
		Number of poles	Range	Max. rating AC 21 (A)	Position	Number of contacts
1	0 277 10	1	PR 12	16		1
1	0 277 11	2	PR 12	16		2
1	0 277 12	3	PR 12	16		3
1	0 277 13	4	PR 12	16		4
		96 x 120 mm box				
1	0 277 16	2	PR 17	20		2
1	0 277 17	3	PR 17	20		3
1	0 277 18	4	PR 17	20		4
1	0 277 21	2	PR 21	25		2
1	0 277 22	3	PR 21	25		3
1	0 277 23	4	PR 21	25		4
		Function: changeover switches				
		Without off - 96 x 120 mm box				
		Number of poles	Range	Max. rating AC 21 (A)	Position	Number of contacts
1	0 277 55	3	PR 12	16		6
1	0 277 56	4	PR 12	16		8
1	0 277 58	4	PR 17	20		8
1	0 277 60	4	PR 21	25		8
1	0 277 62	4	PR 26	32		8
		Without off - 135 x 170 mm box				
1	0 277 64	4	PR 40	50		8
1	0 277 66	4	PR 63	63		8
		With off - 96 x 120 mm box				
1	0 277 25	1	PR 12	16		2
1	0 277 26	2	PR 12	16		4
1	0 277 27	3	PR 12	16		6
1	0 277 28	4	PR 12	16		8
1	0 277 31	2	PR 17	20		4
1	0 277 32	3	PR 17	20		6
1	0 277 33	4	PR 17	20		8
1	0 277 36	2	PR 21	25		4
1	0 277 37	3	PR 21	25		6
1	0 277 38	4	PR 21	25		8
1	0 277 41	2	PR 26	32		4
1	0 277 42	3	PR 26	32		6
1	0 277 43	4	PR 26	32		8

Pack	Cat.Nos	Function: changeover switch (continued)				
		With off - 135 x 170 mm box				
		Number of poles	Range	Max. rating AC 21 (A)	Position	Number of contacts
1	0 277 46	2	PR 40	50		4
1	0 277 47	3	PR 40	50		6
1	0 277 48	4	PR 40	50		8
1	0 277 51	2	PR 63	63		4
1	0 277 52	3	PR 63	63		6
1	0 277 53	4	PR 63	63		8
		Function: 3-way switches				
		With off - 76 x 76 mm box				
		Number of poles	Range	Max. rating AC 21 (A)	Position	Number of contacts
1	0 277 67	1	PR 12	16		3
		With off - 96 x 120 mm box				
1	0 277 68	1	PR 12	16		3
1	0 277 69	2	PR 12	16		6
		Function: 3-phase motor switch				
		Forward/reverse switch, 1 speed				
		Range	Max. rating AC 3 (kW)	Position	Number of contacts	
1	0 277 70	PR 12	4		5	
1	0 277 75	PR 17	7.5		5	
1	0 277 78	PR 21	7.5		5	
1	0 277 81	PR 26	11		5	
1	0 277 84	PR 40	18.5		5	
		Starter 1 way, 1 speed				
1	0 277 71	PR 12	4		8	
1	0 277 76	PR 17	7.5		8	
1	0 277 79	PR 21	7.5		8	
1	0 277 82	PR 26	11		8	
1	0 277 85	PR 40	18.5		8	
		Starter 1 way, 2 speed Dalhander				
1	0 277 72	PR 12	4		8	
1	0 277 77	PR 17	7.5		8	
1	0 277 80	PR 21	7.5		8	
1	0 277 83	PR 26	11		8	
1	0 277 73	PR 12	4		8	