

Protection devices at the output of power supplies

Protection devices at the output

Switched mode, stabilised

		Single-phase, stabilised			
I	Us	Combinable protections	12 V	24 V	48 V
			1 A	Supply	
		Breaker		4 077 76 (1 A)	
1.25 A	Supply			1 466 09	
		Breaker		4 077 77 (2 A)	
1.67 A	Supply	1 466 01			
		Breaker	4 077 77 (2 A)		
1.7 A	Supply		1 466 06		
		Breaker	4 077 77 (2 A)		
2.5 A	Supply		1 466 07	1 466 42	
		Breaker	4 077 78 (3 A)	4 077 78 (3 A)	
3.33/3.2 A	Supply	1 466 02 (3.33 A)	1 466 22 (3,2 A)		
		Breaker	4 077 79 (4 A)	4 077 79 (4 A)	
5 A	Supply	1 466 03	1 466 23	1 466 43	
		Breaker	4 077 80 (6 A)	4 077 80 (6 A)	
6.3 A	Supply	1 466 13			
		Breaker	4 077 81 (8 A)		
10 A	Supply	1 466 14	1 466 24	1 466 44	
		Breaker	4 077 82 (10 A)	4 077 82 (10 A)	
20 A	Supply		1 466 25		
		Breaker	4 077 85 (20 A)		
40 A	Supply		1 466 26		
		Breaker	4 077 88 (40 A)		

		Single/two-phase and three-phase, stabilised			
I	Us	Combinable protections	12 V	24 V	48 V
			2.5 A	Supply	
		Breaker			4 077 78 (3 A)
5 A	Supply		1 466 63	1 466 83	
		Breaker	4 077 80 (6 A)	4 077 80 (6 A)	
10 A	Supply	1 466 54	1 466 64	1 466 84	
		Breaker	4 077 82 (10 A)	4 077 82 (10 A)	
20 A	Supply		1 466 65	1 466 39	
		Breaker	4 077 85 (20 A)	4 077 85 (20 A)	
40 A	Supply		1 466 36		
		Breaker	4 077 88 (40 A)		

Rectified power supplies

		Single-phase, filtered Primary 230/400 V ± 15 V						
I	Us	Protections	12 V		24 V		48 V	
			integral fuse	combine with breaker	integral fuse	combine with breaker	integral fuse	combine with breaker
0.5 A	Supply				0 470 20			
					T 0.5 AL ⁽²⁾	4 077 74 (0.5 A)		
1 A	Supply		0 470 01		0 470 21		0 470 41	
			T 1 AL ⁽²⁾	4 077 76 (1 A)	T 1 AL ⁽²⁾	4 088 80 (1 A)	T 1 AL ⁽²⁾	4 077 76 (1 A)
2.5 A	Supply		0 470 02		0 470 22		0 470 42	
			T 2.5 AL ⁽²⁾	4 077 78 (3 A)	T 2.5 AL ⁽²⁾	4 077 78 (3 A)	T 2.5 AL ⁽²⁾	4 089 54 (3 A)
5 A	Supply		0 470 03		0 470 23		0 470 43	
			T 5 AL ⁽²⁾	4 077 80 (6 A)	T 5 AL ⁽²⁾	4 077 80 (6 A)	T 5 AL ⁽²⁾	4 089 56 (6 A)
10 A	Supply		0 470 04		0 470 24		0 470 44	
			T 10 AL ⁽²⁾	4 077 82 (10 A)	T 10 AL ⁽²⁾	4 077 82 (10 A)	T 10 AL ⁽²⁾	4 077 82 (10 A)
15 A	Supply				0 470 25		0 470 45	
					0 133 16 ⁽³⁾	4 077 84 (16 A)	0 133 16 ⁽³⁾	4 077 84 (16 A)
25 A	Supply		0 470 06		0 470 26		0 470 46	
			0 133 25 ⁽³⁾	4 077 86 (25 A)	0 133 25 ⁽³⁾	4 077 86 (25 A)	0 133 25 ⁽³⁾	4 077 86 (25 A)
40 A	Supply				0 470 28			
					0 133 40 ⁽³⁾	4 077 88 (40 A)		
50 A	Supply				0 470 29			
					0 133 50 ⁽³⁾	4 077 89 (50 A)		