


 Support frame and plate selection charts **p. 594-603**

Mechanisms supplied with square rocker plates, to be equipped with support frames (p. 585) and plates (p. 594 to 603)

Pack	Cat.Nos	Thermostats	Pack	Cat.Nos	Fan controllers
		Electronic room thermostat Control knob with index and adjustable segments for min. and max. settings Adjustable range from 5 °C to 30 °C (+/- 0.5 °C) Power supply: 230 V~ - 50/60 Hz One potential free changeover contact output Suitable for controlling heated ceilings and underfloor heating - LV use breaking capacity: 8 A - 250 V~ - resistive inductive circuit 2 A - 250 V~ - inductive circuit - ELV use breaking capacity: 12 to 48 V~ - 12 to 24 V=, from 1 mA min. to 500 mA max. 2 modules <ul style="list-style-type: none"> ○ White ● Magnesium ● Champagne ● Soft Alu 			2 modules AC speed control - 4 positions <ul style="list-style-type: none"> ○ White ● Magnesium ● Champagne ● Soft Alu Rotary speed controller for fan Operates 40 to 400 VA limit switch For progressive speed control of ceiling fan <ul style="list-style-type: none"> ○ White ● Magnesium ● Champagne ● Soft Alu Fan step regulator - 100 W <ul style="list-style-type: none"> ○ White ● Magnesium ● Champagne ● Soft Alu
1	5 722 03		1	5 722 17	
1	5 727 03		1	5 727 17	
1	5 727 06		1	5 727 87	
1	5 727 05		1	5 727 86	
		Thermostat for electric floor heating With one potential free N/O contact and LED 16 A - 230 V~ Adjustable range from 7 °C to 40 °C 2 modules <ul style="list-style-type: none"> ○ White ● Magnesium ● Champagne ● Soft Alu 			Curtain switches 1 module Curtain switch centre off <ul style="list-style-type: none"> ○ White ● Magnesium ● Champagne ● Soft Alu Curtain switch centre retract Push-button action <ul style="list-style-type: none"> ○ White ● Magnesium ● Champagne ● Soft Alu
1	5 722 63		5	5 722 02	
1	5 727 63		5	5 727 02	
1	5 727 08		5	5 700 52	
1	5 727 07		5	5 710 52	
					Electric roller blind controllers - 250 V~ For control via automatic box (N/O mechanism) Double push-button - 10 A 2 modules <ul style="list-style-type: none"> ○ White ● Magnesium ● Champagne ● Soft Alu For direct control of a motor (mechanism with fixed positions) Double push-button - 10 A 2 modules <ul style="list-style-type: none"> ○ White ● Magnesium ● Champagne ● Soft Alu
			10	5 722 19	
			10	5 727 19	
			10	5 729 43	
			10	5 729 42	
			10	5 722 20	
			10	5 727 20	
			10	5 700 54	
			10	5 710 54	

