

Arteor™

lighting control, emergency push-buttons



5 720 55



5 723 63

Support frame and plate selection charts **p. 594-603**

Mechanisms supplied with rocker plates, to be equipped with support frames (p. 585) and plates (p. 594 to 603)

Pack	Cat.Nos	Time delay switches
		Interference suppression conforming to standard EN 55022 For timer control of a circuit with the following loads: - 1000 W incandescent and halogen 230 V~ - 2300 W resistive (heating) - 400 VA fluorescent and ELV halogen Adjustable from 25 s to 15 min It is possible to install a number of timer switches in parallel on the same circuit With integrated LED 2-wire installation in box min. depth 40 mm 2 modules
1	5 720 55	<ul style="list-style-type: none"> ○ White ● Magnesium ● Champagne ● Soft Alu
1	5 740 84	
1	5 741 38	
1	5 741 37	

Pack	Cat.Nos	Single pole latching relays 10 A - 250 V~
		Used to bring functions with low breaking capacity close to the application - Resistive: 3000 W - Incandescent: 1800 W - LV halogen: 1800 W - Fluorescent: 400 VA - Motors (roller blind type): 530 W 2 modules
1	5 722 27	<ul style="list-style-type: none"> ○ White ● Magnesium ● Champagne ● Soft Alu
1	5 727 27	
1	5 729 47	
1	5 729 46	

Pack	Cat.Nos	Emergency stop mushroom head push-buttons 10 A - 250 V~
		N/O + N/C 2 modules With key Unlock with RONIS key no. 601
1	5 723 63	<ul style="list-style-type: none"> ● Yellow/red
1	5 723 62	<ul style="list-style-type: none"> ● Yellow/red

Arteor™

double pole switches, cooker control unit



5 720 87



5 720 88

Support frame and plate selection charts **p. 594-603**

Mechanisms supplied with rocker plates, to be equipped with plate (p. 594-601)

Support frame not needed

Pack	Cat.Nos	Double pole switches 40 A - 250 V~
		Conform to EN 60669-1: 2000 and SANS 164-1 Captive terminal screws For flush-mounting box to be min. 48 mm deep Use US plate 4" x 4" - 2 modules
5	5 720 81	<ul style="list-style-type: none"> ○ White ● Magnesium ● Champagne ● Soft Alu
5	5 725 81	
5	5 721 95	
5	5 721 94	

Pack	Cat.Nos	Double pole switch + neon
5	5 720 82	<ul style="list-style-type: none"> ○ White ● Magnesium ● Champagne ● Soft Alu
5	5 725 82	
5	5 721 97	
5	5 721 96	

Pack	Cat.Nos	Double pole switches 45 A - 250 V~
		Conform to EN 60669-1: 2000 Captive terminal screws For flush-mounting box to be min. 48 mm deep
5	5 720 80	<ul style="list-style-type: none"> ○ White ● Magnesium ● Champagne ● Soft Alu
5	5 725 80	
5	5 724 92	
5	5 724 85	

Pack	Cat.Nos	Double pole switch + neon - 2-gang
		Use BS plate 3 modules
5	5 720 80	<ul style="list-style-type: none"> ○ White ● Magnesium ● Champagne ● Soft Alu
5	5 725 80	
5	5 721 99	
5	5 721 98	

Pack	Cat.Nos	Cooker control unit 250 V~
		Conform to BS 4177: 1992 45 A double pole switch + 13 A double pole switched socket outlet Use special plate Cat.No 5 751 50
5	5 720 88	<ul style="list-style-type: none"> ○ White