


 Support frame and plate selection charts **p. 594-603**

Can be integrated in any support
 Mechanisms supplied with rocker plates, to be equipped with support frames (p. 585) and plates (p. 594-603)
 Equipped with connectors with quick toolless connection
 Take single-core cables from AWG 22 up to AWG 26, and AWG 26 multicore cables
 T568A and B marking with colour codes
 Compliant with ISO/IEC 11 801, EN 50173 and ANSI/TIA 568 standards

Pack	Cat.Nos	Cat. 6A sockets
		360° metal shielding
		STP - 1 module
10	5 723 06	○ White
10	5 728 06	● Magnesium
10	5 728 46	● Champagne
10	5 728 45	● Soft Alu
10	5 723 51	○ White with orange shutter
10	5 728 51	● Magnesium with orange shutter
10	5 728 48	● Champagne with orange shutter
10	5 728 47	● Soft Alu with orange shutter
10	5 723 52	○ White with green shutter
10	5 728 52	● Magnesium with green shutter
10	5 728 61	● Champagne with green shutter
10	5 728 60	● Soft Alu with green shutter
		STP with controlled access - 2 modules Supplied with 2 keys for 5 sockets
5	5 723 50	○ White with red shutter
5	5 728 50	● Magnesium with red shutter
5	5 728 63	● Champagne with red shutter
5	5 728 62	● Soft Alu with red shutter
		UTP - 1 module
10	5 723 49	○ White
10	5 728 49	● Magnesium
10	5 728 65	● Champagne
10	5 728 64	● Soft Alu
10	5 723 58	○ White with orange shutter
10	5 728 58	● Magnesium with orange shutter
10	5 728 69	● Champagne with orange shutter
10	5 728 68	● Soft Alu with orange shutter
10	5 723 59	○ White with green shutter
10	5 728 59	● Magnesium with green shutter
10	5 728 67	● Champagne with green shutter
10	5 728 66	● Soft Alu with green shutter
		UTP with controlled access - 2 modules Supplied with 2 keys for 5 sockets
5	5 723 57	○ White with red shutter
5	5 728 57	● Magnesium with red shutter
5	5 728 72	● Champagne with red shutter
5	5 728 71	● Soft Alu with red shutter

Pack	Cat.Nos	Cat. 6 sockets
		UTP - 1 module
10	5 723 02	○ White
10	5 728 02	● Magnesium
10	5 700 57	● Champagne
10	5 710 57	● Soft Alu
10	5 723 54	○ White with orange shutter
10	5 728 54	● Magnesium with orange shutter
10	5 728 74	● Champagne with orange shutter
10	5 728 73	● Soft Alu with orange shutter
10	5 723 55	○ White with green shutter
10	5 728 55	● Magnesium with green shutter
10	5 728 80	● Champagne with green shutter
10	5 728 79	● Soft Alu with green shutter
		UTP - 2 modules
10	5 723 14	○ White - square version
10	5 728 14	● Magnesium - square version
10	5 700 59	● Champagne - square version
10	5 710 59	● Soft Alu - square version
10	5 723 24	○ White - round version
10	5 728 24	● Magnesium - round version
10	5 728 81	● Soft Alu - round version
		UTP with controlled access - 2 modules Supplied with 2 keys for 5 sockets
5	5 723 53	○ White with red shutter
5	5 728 53	● Magnesium with red shutter
5	5 728 87	● Champagne with red shutter
5	5 728 86	● Soft Alu with red shutter
		UTP with retractable cord - 4 modules Cord (0.9 m) winds up automatically with a pushbutton
1	5 723 39	○ White
1	5 728 39	● Magnesium
1	5 728 89	● Champagne
1	5 728 88	● Soft Alu
		FTP - 1 module
10	5 723 22	○ White
10	5 728 22	● Magnesium
10	5 728 91	● Champagne
10	5 728 90	● Soft Alu
		FTP - 2 modules
10	5 723 16	○ White
10	5 728 16	● Magnesium
10	5 728 93	● Champagne
10	5 728 92	● Soft Alu
		STP shielded - 1 module
10	5 723 23	○ White
10	5 728 23	● Magnesium
10	5 728 95	● Champagne
10	5 728 94	● Soft Alu
		STP shielded - 2 modules
10	5 723 17	○ White
10	5 728 17	● Magnesium
10	5 728 97	● Champagne
10	5 728 96	● Soft Alu