

Arteor™ with Netatmo - International

connected cable outlet, connected 4-step fan regulator

Step 2: Connected products



Home + Control



0 648 79



5 742 48

Used to complete your connected installation, require prior installation of a gateway pack for connected installation Zigbee Certified Product

Pack	Cat.Nos	Connected cable outlet
1	0 648 79	<p>Conform to IEC 60669-2-1 Enables remote control of electrical devices Wiring compatible with pilot wire Can be controlled by one or several wireless light switches 3000 W max. (protected against overloads) Functions: - ON/OFF, pilot wire management - instantaneous power measurement and daily/monthly consumption monitoring with configurable sending of notifications (defect, consumption, etc.) Supplied with mounting support, cover plate and worksite protection Multi-gang fixing not possible</p> <p>○ White ● Magnesium ● Champagne ● Soft Alu</p>
1	0 648 83	
1	0 648 82	
1	0 648 98	

Pack	Cat.Nos	Connected 4-step fan regulator with neutral 100 W - 230 V~
1	5 742 48	<p>Mechanisms supplied with cover plates, to be equipped with support frames (p. 614) and plates (p. 594-603) For local or remote control via the Home + Control App. and voice assistants Can be controlled by one or several wireless fan switches (p. 613) Compatible with all asynchronous fan engines AC 230 V~ 100 W maximum Not compatible with DC fan engines Can be installed in place of an existing fan control in a flush-mounting box min. depth 40 mm Neutral required LED indicators to visualize the fan speed 2 modules</p> <p>○ White ● Magnesium ● Champagne ● Soft Alu</p>
1	5 742 50	
1	5 742 51	
1	5 742 49	

Arteor™ with Netatmo - International

connected curtain/roller blind switches

Step 2: Connected products



Home + Control



5 742 04



0 676 96

Support frame and plate selection charts p. 594 to 603

Used to complete your connected installation, require prior installation of a gateway pack for connected installation Zigbee Certified Product

Pack	Cat.Nos	Connected curtain/roller blind switch 500 VA
1	5 742 04	<p>Mechanisms supplied with cover plates, to be equipped with support frames (p. 614) and plates (p. 594-603) For local and remote control of a 230 V~ roller blind (raise/lower/stop functions and level management) Compatible with roller blinds with mechanical or electronic stop, not compatible with radio-controlled roller blinds Can be paired with one or more roller blind wireless switches Can be installed in place of an existing roller blind switch in a flush-mounting box depth 35 mm 1 module - with neutral</p> <p>○ White ● Magnesium ● Champagne ● Soft Alu</p>
1	5 742 22	
1	5 742 31	
1	5 742 13	

Pack	Cat.Nos	Connected curtain/roller blind micromodule 500 VA - IP 44
1	0 676 97	<p>For local and remote control of a 230 V~ roller blind (raise/lower/stop functions and level management) Compatible with roller blinds with mechanical or electronic stop, not compatible with radio-controlled roller blinds Can be paired with one or more roller blind wireless switches To be installed in the ceiling box or roller blind box to connect a new or existing roller blind</p>

Pack	Cat.Nos	Connected module for garage door and gate (dry contact)
1	0 676 96	<p>Enables open/close control of a garage door or gate, locally, remotely or via voice assistant Status display (open/closed/ level) in the Home + Control App. Can be controlled using a curtain/roller blind wireless control (p. 612) or a wireless scene control (e.g. Cat.No 0 676 95 p. 612) Supplied with 2 wired position sensors Can be installed in an IP 55 Plexo box 80 x 80 mm or larger and in parallel of an existing mechanical push-button Fitted with 2 removable fixing points Compatible with any garage door and gate engine equipped with a dry contact entry for mechanical push-button</p>