

Arteor™ with Netatmo - International

connected wireless light controls



Home + Control

Step 2: Connected products



5 742 05



5 742 52



5 742 89



5 744 24

Support frame and plate selection charts **p. 594 to 603**

Used to complete your connected installation, require prior installation of a gateway pack for connected installation. Zigbee Certified Product

Pack	Cat.Nos	Wireless light switches	Pack	Cat.Nos	Wireless batteryless light switches
1	5 742 05	<p>Used to add an extra control for wired switches, micromodules, socket outlets and cable outlets Easy pairing by tapping the wired product or by using the Home + Control App. Supplied with CR2032 3 V long-life battery for power supply LED function for low battery indication</p> <p>Surface-mounting version, 1-gang Supplied with cover plate, multi-standard support frame (with removable fins) and removable stickers for fixing the control unit on any substrate To be equipped with 2-module plates (p. 594-603) Controls up to 20 wired products</p> <ul style="list-style-type: none"> ○ White ● Magnesium ● Champagne ● Soft Alu 	1	5 742 39	<p>Extra-slim, maintenance-free device without any battery Used to add an extra control for wired switches, micromodules, socket outlets and cable outlets Energy harvesting mechanism that generates by itself the energy required for the switching process Qualified for 1 million cycles. Smooth and silent switching. Easy pairing by tapping the wired product (switches, micromodules, socket outlets) or by using the Home + Control App. Supplied with cover plate, multi-standard support frame (with removable fins) and removable stickers for fixing the control unit on any substrate To be equipped with 2-module plates (p. 594-603)</p> <p>1-gang Controls up to 20 wired products</p> <ul style="list-style-type: none"> ○ White ● Magnesium ● Champagne ● Soft Alu
1	5 742 23		1	5 743 24	
1	5 742 32		1	5 742 55	
1	5 742 14		1	5 742 10	
1	5 742 44	<p>Surface-mounting version, 2-gang Supplied with cover plate, multi-standard support frame (with removable fins) and removable stickers for fixing the control unit on any substrate To be equipped with 2-module plates (p. 594-603) Controls up to 2x20 wired products</p> <ul style="list-style-type: none"> ○ White ● Magnesium ● Champagne ● Soft Alu 	1	5 742 89	<p>2-gang Controls up to 2x20 wired products</p> <ul style="list-style-type: none"> ○ White ● Magnesium ● Champagne ● Soft Alu
1	5 742 46		1	5 743 25	
1	5 742 47		1	5 748 38	
1	5 742 45		1	5 742 96	
1	5 742 91	<p>Flush-mounting version, 1 module Mechanism supplied with cover plate, to be equipped with support frames (p. 614) and plates (p. 594-603) Can be installed in a flush-mounting box depth 35 mm Allows aesthetic consistency for modular installation Controls up to 20 wired products</p> <ul style="list-style-type: none"> ○ White ● Magnesium ● Champagne ● Soft Alu 	<p>Wireless switches for multicolour lighting Allow to directly control up to 20 Zigbee 3.0 compatible multi-colour lighting (e.g. Ledvance Smart+ Zigbee, Phillips Hue...). To be associated with the lighting in the Home + Control App. Allow ON/OFF and dimming control of 3 light moods which have to be preset in the Home + Control App. Supplied with CR2032 3 V long-life battery for power supply. LED function for low battery indication Not compatible with Wi-Fi lighting</p> <p>Surface-mounting version, 2-gang Supplied with cover plate, multi-standard support frame (with removable fins) and removable stickers for fixing the control unit on any substrate To be equipped with 2-module plates (p. 594-603)</p> <ul style="list-style-type: none"> ○ White ● Magnesium ● Champagne ● Soft Alu 		
1	5 742 76				
1	5 743 26				
1	5 742 75				
1	5 742 52	<p>Wireless motion sensor IP 44 Allows to control up to 20 wired switches, micromodules, socket outlets and cable outlets Easy pairing by tapping the wired products or by using the Home + Control App. Supplied with 2 x AA battery. For indoor and outdoor use Recommended distance between 2 sensors: 6 m Recommended installation height: 2.5 m Time delay adjustable from 15 s to 15 min Range: 8 m. Detection angle: 140° Sensor range adjustable from 2 m to 8 m Light level threshold adjustable from 1 to 1000 lux</p>	1	5 744 34	<p>Flush-mounting version, 1 module Mechanism supplied with cover plate, to be equipped with support frames (p. 614) and plates (p. 594-603) Can be installed in a flush-mounting box depth 35 mm Allows aesthetic consistency for modular installation</p> <ul style="list-style-type: none"> ○ White ● Magnesium ● Champagne ● Soft Alu
		1	5 744 35		
		1	5 744 36		
		1	5 744 37		
1	0 676 94	<p>Wireless switch ON/OFF module Allows to transform a mechanical 2-way switch or push-button into a wireless ON/OFF switch. Small size for easy integration into the wall box. To be paired with one connected switch, micromodule, socket outlet. Supplied with CR2032 3 V long-life battery for power supply</p>	1	5 744 24	<p>Wireless switches for multicolour lighting Allow to directly control up to 20 Zigbee 3.0 compatible multi-colour lighting (e.g. Ledvance Smart+ Zigbee, Phillips Hue...). To be associated with the lighting in the Home + Control App. Allow ON/OFF and dimming control of 3 light moods which have to be preset in the Home + Control App. Supplied with CR2032 3 V long-life battery for power supply. LED function for low battery indication Not compatible with Wi-Fi lighting</p> <p>Surface-mounting version, 2-gang Supplied with cover plate, multi-standard support frame (with removable fins) and removable stickers for fixing the control unit on any substrate To be equipped with 2-module plates (p. 594-603)</p> <ul style="list-style-type: none"> ○ White ● Magnesium ● Champagne ● Soft Alu
		1	5 744 25		
		1	5 744 26		
		1	5 744 27		

Red catalogue numbers: New products