

## Arteor™ with Netatmo connected wireless light controls (continued)

### Step 2: Connected products



Home + Control




5 742 52



0 676 94

Used to complete your connected installation, require prior installation of a gateway pack for connected installation  
Zigbee Certified Product

Pack	Cat.Nos	Wireless motion sensor IP 44
1	5 742 52	 <p>Allows to control up to 20 wired switches, micromodules, socket outlets and cable outlets Easy pairing by tapping the wired products or by using the Home + Control App. Supplied with 2 x AA battery</p> <p>For indoor and outdoor use Recommended distance between 2 sensors: 6 m Recommended installation height: 2.5 m Time delay adjustable from 15 s to 15 min Range: 8 m Detection angle: 140° Sensor range adjustable from 2 m to 8 m With ON/OFF test buttons Light level threshold adjustable from 1 to 1000 lux</p>
1	0 676 94	 <p>Allows to transform a mechanical 2-way switch or push-button into a wireless ON/OFF switch. Small size for easy integration into the wall box To be paired with one connected switch, micromodule, socket outlet Supplied with CR2032 3V long-life battery for power supply</p>

## Arteor™ with Netatmo - British standard connected wireless scene switches

### Step 2: Connected products



Home + Control





5 746 53



5 742 87

 Plate selection charts **p. 594 to 603**

Used to complete your connected installation, require prior installation of a gateway pack for connected installation  
Zigbee Certified Product

Pack	Cat.Nos	Wake up/Sleep wireless switch
1	5 746 51	 <p>Used to add 2 extra scenes to a connected installation Preset Wake up/Sleep life scenes which can be customised in the Home + Control App. Supplied with CR2032 3 V long-life battery for power supply Easy access to the battery for maintenance LED function for low battery indication Supplied with cover plate, multi-standard support frame (with removable fins) and removable stickers for fixing the control unit on any substrate To be equipped with 2-module plates (p. 594 to 603)</p> <p><b>1-gang</b></p> <ul style="list-style-type: none"> <li>○ White</li> <li>● Magnesium</li> <li>● Champagne</li> <li>● Soft Alu</li> </ul>
1	5 746 52	
1	5 746 54	
1	5 746 53	
1	5 742 87	 <p>Extra-slim, maintenance-free device without any battery Used to add 2 extra scenes to a connected installation Energy harvesting mechanism that generates by itself the energy required for the switching process Qualified for 1 million cycles Smooth and silent switching Preset Wake up/Sleep life scenes which can be customised in the Home + Control App.</p> <p><b>1-gang</b></p> <p>Supplied with cover plate, multi-standard support frame (with removable fins) and removable stickers for fixing the control unit on any substrate To be equipped with 2-module plates (p. 594 to 603)</p> <ul style="list-style-type: none"> <li>○ White</li> <li>● Magnesium</li> <li>● Champagne</li> <li>● Soft Alu</li> </ul>
1	5 743 22	
1	5 748 36	
1	5 742 93	