



6 180 41



6 180 49



6 180 58



6 180 44

Material: Thermoplastic with glossy finish
Dimensions: 86 x 86 x 9.5 mm (1-gang) / 86 x 146 x 9.5 mm (2-gang)
Supplied with 2 screws M3.5 for BS boxes

Pack	Cat.Nos	British Standard socket outlets 13 A - 250 V~
10	6 180 41	Conform to BS 1363-2 1-gang single pole switched ○ White
5	6 180 46	2-gang single pole switched ○ White
10	6 180 40	1-gang unswitched ○ White
5	6 180 45	2-gang unswitched ○ White
10	6 180 43	1-gang double pole switched ○ White
5	6 180 73	1-gang double pole switched 2 earth terminal ○ White
5	6 180 48	2-gang double pole switched ○ White
10	6 180 42	1-gang single pole switched + neon ○ White
5	6 180 47	2-gang single pole switched + neon ○ White
5	6 180 49	2-gang single pole switched with red cover + neon ● Red

Pack	Cat.Nos	British Standard socket outlets 13 A - 250 V~ with USB charger
1	6 180 58	Conform to BS 1363-2 Conform to IEC 60950-1 1-gang single pole switched with USB Type-A - 3 A - 5 V_{DC} - 15 W Consumption in passive mode < 0.08 W ○ White
1	6 180 57	1-gang unswitched with USB Type-A - 3 A - 5 V_{DC} - 15 W Consumption in passive mode < 0.08 W ○ White
1	6 180 30	1-gang unswitched with USB Type-C - 3 A - 5 V_{DC} - 15 W Consumption in passive mode < 0.08 W ○ White
1	6 180 44	2-gang single pole switched with USB Type-A + Type-C - 3 A - 5 V_{DC} - 15 W Consumption in passive mode < 0.08 W ○ White
10	6 180 51	Conform to BS 546 1-gang single pole switched ○ White
5	6 180 52	1-gang single pole switched + neon ○ White
5	6 180 53	2-gang single pole switched ○ White
10	6 180 54	Conform to BS 546 1-gang single pole switched ○ White