



6 180 64



6 180 69



6 180 55

Material: Thermoplastic with glossy finish
 Dimensions: 86 x 86 x 9.5 mm (1-gang) / 86 x 146 x 9.5 mm (2-gang)
 Supplied with 2 screws M3.5 for BS boxes

Euro/US socket outlets - 16 A - 250 V \sim / 15 A - 127 V \sim

Pack	Cat.Nos	Description
10	6 180 62	1-gang 2 x 2P ○ White
10	6 180 90	1-gang 2 x 2P switched ○ White
10	6 180 64	1-gang 2 x 2P+E ○ White
10	6 180 56	German Standard socket outlet 16 A - 250 V\sim 1-gang 2P+E with shutters for child protection ○ White
10	6 180 67	Multistandard switched socket outlet 15 A 127 V\sim / 16 A 250 V\sim 1-gang ○ White
5	6 180 69	2-gang ○ White

Multistandard switched socket and Euro/ US socket outlets

Pack	Cat.Nos	Description
10	6 180 65	1-gang ○ White
1	6 180 59	Multistandard switched socket outlets 16 A 250 V\sim / 15 A - 127 V\sim with USB charger Shutterd for child safety USB charger conform to IEC 60950-1 1-gang 2P+E with USB Type-A - 3 A - 5 V\dots - 15 W Consumption in passive mode < 0.08 W ○ White
1	6 180 55	2-gang 2 x 2P+E with USB Type-A + Type-C - 3 A - 5 V\dots - 15 W Consumption in passive mode < 0.08 W ○ White