

ELOÉ™
fused connection units and cable outlets


6 180 82

6 180 85

Material: Thermoplastic with glossy finish
 Dimensions: 86 x 86 x 9.5 mm (1-gang) / 86 x 146 x 9.5 mm (2-gang)
 Supplied with 2 screws M3.5 for BS boxes

Fused connection units 13 A

Pack	Cat.Nos	Description
10	6 180 80	Unswitched + cord outlet ○ White
5	6 180 81	Switched + cord outlet ○ White
10	6 180 60	Unswitched + neon + cord outlet ○ White
10	6 180 82	Switched + neon + cord outlet ○ White

Cable outlets
 Conform to BS 5733

10	6 180 85	20 A - 250 V~ ○ White
10	6 180 86	45 A - 250 V~ ○ White

ELOÉ™
blanking plates and accessories


6 180 28

6 180 37 + 5 720 72

6 176 36 + 6 180 30

Blanking plates

Pack	Cat.Nos	Description
10	6 180 28	1-gang ○ White
10	6 180 39	2-gang ○ White

Arteur adaptor

10	6 180 37	Allows the integration of 2-module Arteur mechanisms such as R.C.B.O., automatic switch, skirting light, USB charger, etc 1-gang ○ White
----	----------	--

Fixing accessories

4	6 176 36	Splash-proof cover Mainly for socket protection IP 55 with or without plug engaged Space inside : 86 x 86 mm External dimensions : 129,2 x 107,2 x 54,1 mm ● Mist grey
---	----------	---

Surface-mounting boxes

8	6 133 50	Conform to BS 5733 Depth 35 mm 1-gang ○ White
4	6 133 51	2-gang ○ White

For integration of Arteur functions, see **Arteur offer p. 558**

