

Belanko™ S

single pole switches and push-buttons



6 176 01



6 176 05



6 176 07



6 176 11



6 176 16

Conform to BS EN 60669-1
Material: Thermoplastic with glossy finish
Dimensions: 86 x 86 x 9.5 mm (1-gang)
Supplied with 2 screws M3.5 for BS boxes

Single pole switches 16 AX - 250 V~

Pack	Cat.Nos	
10	6 176 00	1-gang 1-way switch <input type="radio"/> White <input checked="" type="radio"/> Anthracite <input type="radio"/> Ivory
10	6 177 00	
10	6 178 00 ¹	
10	6 176 01	1-gang 2-way switch <input type="radio"/> White <input checked="" type="radio"/> Anthracite <input type="radio"/> Ivory
10	6 177 01	
10	6 178 01 ¹	
10	6 176 02	2-gang 1-way switch Two inputs, two outputs <input type="radio"/> White <input checked="" type="radio"/> Anthracite <input type="radio"/> Ivory
10	6 177 02	
10	6 178 02 ¹	
10	6 176 03	2-gang 2-way switch <input type="radio"/> White <input checked="" type="radio"/> Anthracite <input type="radio"/> Ivory
10	6 177 03	
10	6 178 03 ¹	
10	6 176 09	1-gang intermediate switch <input type="radio"/> White <input checked="" type="radio"/> Anthracite <input type="radio"/> Ivory
10	6 177 09	
10	6 178 09 ¹	
10	6 176 04	3-gang 1-way switch <input type="radio"/> White <input checked="" type="radio"/> Anthracite <input type="radio"/> Ivory
10	6 177 04	
10	6 178 04 ¹	
10	6 176 05	3-gang 2-way switch <input type="radio"/> White <input checked="" type="radio"/> Anthracite <input type="radio"/> Ivory
10	6 177 05	
10	6 178 05 ¹	
10	6 176 06	4-gang 1-way switch <input type="radio"/> White <input checked="" type="radio"/> Anthracite <input type="radio"/> Ivory
10	6 177 06	
10	6 178 06 ¹	
10	6 176 07	4-gang 2-way switch <input type="radio"/> White <input checked="" type="radio"/> Anthracite <input type="radio"/> Ivory
10	6 177 07	
10	6 178 07 ¹	

Single pole switches 20 AX - 250 V~

Pack	Cat.Nos	
10	6 176 20	1-gang 1-way switch <input type="radio"/> White <input checked="" type="radio"/> Anthracite <input type="radio"/> Ivory
10	6 177 20	
10	6 178 20 ¹	
10	6 176 21	1-gang 2-way switch <input type="radio"/> White <input checked="" type="radio"/> Anthracite <input type="radio"/> Ivory
10	6 177 21	
10	6 178 21 ¹	
10	6 176 22	2-gang 1-way switch Two inputs, two outputs <input type="radio"/> White <input checked="" type="radio"/> Anthracite <input type="radio"/> Ivory
10	6 177 22	
10	6 178 22 ¹	
10	6 176 23	2-gang 2-way switch <input type="radio"/> White <input checked="" type="radio"/> Anthracite <input type="radio"/> Ivory
10	6 177 23	
10	6 178 23 ¹	
10	6 176 24	3-gang 1-way switch <input type="radio"/> White <input checked="" type="radio"/> Anthracite <input type="radio"/> Ivory
10	6 177 24	
10	6 178 24 ¹	
10	6 176 25	3-gang 2-way switch <input type="radio"/> White <input checked="" type="radio"/> Anthracite <input type="radio"/> Ivory
10	6 177 25	
10	6 178 25 ¹	

Push-buttons 6 A - 250 V~

10	6 176 10	1-gang <input type="radio"/> White <input checked="" type="radio"/> Anthracite <input type="radio"/> Ivory
10	6 177 10	
10	6 178 10 ¹	
10	6 176 15	2-gang Two inputs, two outputs <input type="radio"/> White <input checked="" type="radio"/> Anthracite <input type="radio"/> Ivory
10	6 177 15	
10	6 178 15 ¹	
10	6 176 11	Bell push <input type="radio"/> White <input checked="" type="radio"/> Anthracite <input type="radio"/> Ivory
10	6 177 11	
10	6 178 11 ¹	
10	6 176 16	2-gang for shutters Two inputs, two outputs <input type="radio"/> White <input checked="" type="radio"/> Anthracite <input type="radio"/> Ivory
10	6 177 16	
10	6 178 16 ¹	

Red catalogue numbers: New products

1: Available on request