

Belanko™ S

socket outlets (continued)



6 176 64



6 176 67



6 176 55

Material: Thermoplastic with glossy finish
 Dimensions: 86 x 86 x 9.5 mm (1-gang) / 86 x 146 x 9.5 mm (2-gang). Supplied with 2 screws M3.5 for BS boxes

Pack	Cat.Nos	British Standard socket outlets 13 A - 250 V~ with USB charger
10	6 176 50	Conform to BS 546 1-gang unswitched ○ White ● Anthracite ○ Ivory
10	6 177 50	
10	6 178 50 ¹	
10	6 176 51	1-gang single pole switched ○ White ● Anthracite ○ Ivory
10	6 177 51	
10	6 178 51 ¹	
10	6 176 52	1-gang single pole switched + neon ○ White ● Anthracite ○ Ivory
10	6 177 52	
10	6 178 52 ¹	
10	6 176 53	2-gang single pole switched ○ White ● Anthracite ○ Ivory
10	6 177 53	
10	6 178 53 ¹	

Pack	Cat.Nos	British Standard socket outlets 5 A - 250 V~
10	6 176 54	Conform to BS 546 1-gang single pole switched ○ White ● Anthracite ○ Ivory
10	6 177 54	
10	6 178 54 ¹	

Pack	Cat.Nos	Euro/US socket outlets - 10 A - 250 V~ / 15 A - 127 V~
10	6 176 62	1-gang - 2 x 2P ○ White ● Anthracite ○ Ivory
10	6 177 62	
10	6 178 62 ¹	
10	6 176 90	1-gang - 2 x 2P switched ○ White ● Anthracite ○ Ivory
10	6 177 90	
10	6 178 90 ¹	
10	6 176 64	1-gang - 2 x 2P+E ○ White ● Anthracite ○ Ivory
10	6 177 64	
10	6 178 64 ¹	

Pack	Cat.Nos	German Standard socket outlet 16 A - 250 V~
10	6 176 56	1-gang - 2P+E with shutters for child protection ○ White ● Anthracite ○ Ivory
10	6 177 56	
10	6 178 56 ¹	
10	6 176 67	Multistandard switched socket outlet 1-gang ○ White ● Anthracite ○ Ivory
10	6 177 67	
10	6 178 67 ¹	
4	6 176 69	2-gang ○ White ● Anthracite ○ Ivory
4	6 177 69	
4	6 178 69 ¹	
10	6 176 61	Multistandard + Euro/US switched socket outlet 1-gang ○ White

Pack	Cat.Nos	Multistandard switched socket outlets 16 A - 250 V~ / 15 A - 127 V~ with USB charger
1	6 176 59A	Shuttered for child safety USB charger conform to IEC 60950-1 1-gang - 2P+E with USB Type-A - 3 A - 5 V_{DC} - 15 W Consumption in passive mode < 0.07 W ○ White ● Anthracite ○ Ivory
1	6 177 59A	
1	6 178 59A ¹	
1	6 176 68A	1-gang - 2P+E with USB Type-C - 18 W Fast charge feature: Power Delivery Consumption in passive mode < 0.07 W ○ White ● Anthracite ○ Ivory
1	6 177 68A	
1	6 178 68A ¹	
1	6 176 55	2-gang - 2 x 2P+E with USB Type-A + Type-C - 3 A - 5 V_{DC} - 15 W Consumption in passive mode < 0.08 W ○ White ● Anthracite ○ Ivory
1	6 177 55	
1	6 178 55 ¹	

1: Available on request