



2 824 32



2 824 33-C



2 824 83A



2 824 43

Material: Polycarbonate front cover plates
Dimensions: 86 x 88 mm (1-gang) / 146 x 88 mm (2-gang)
Supplied with 2 screws M 3.5 for BS boxes. Supplied complete with plate. All sockets integrate child protection

Pack	Cat.Nos	British Standard socket outlets 13 A - 250 V~	Pack	Cat.Nos	British Standard socket outlets 13 A - 250 V~ - with USB chargers
8	2 824 30	<p>Conform to BS 1363-2</p> <p>1-gang - unswitched</p> <ul style="list-style-type: none"> ○ White ● Matt Black ● Rose Gold ● Champagne ● Dark Silver 	5	2 824 40A	<p>Conform to BS 1363-2</p> <p>Consumption in passive mode < 0.08 W</p> <p>1-gang - unswitched, with USB charger Type-A - 3 A - 5 V_{DC} - 15 W</p> <ul style="list-style-type: none"> ○ White ● Matt Black ● Rose Gold ● Champagne ● Dark Silver
8	2 824 30-C		5	2 824 40A-C	
8	2 824 30-C1		5	2 824 40A-C1	
8	2 824 30-C2		5	2 824 40A-C2	
8	2 824 30-C3		5	2 824 40A-C3	
8	2 824 32	<p>1-gang single pole - switched</p> <ul style="list-style-type: none"> ○ White ● Matt Black ● Rose Gold ● Champagne ● Dark Silver 	5	2 824 41A	<p>1-gang single pole - switched, with USB charger Type-A - 3 A - 5 V_{DC} - 15 W</p> <ul style="list-style-type: none"> ○ White ● Matt Black ● Rose Gold ● Champagne ● Dark Silver
8	2 824 32-C		5	2 824 41A-C	
8	2 824 32-C1		5	2 824 41A-C1	
8	2 824 32-C2		5	2 824 41A-C2	
8	2 824 32-C3		5	2 824 41A-C3	
8	2 824 86	<p>1-gang double pole - switched</p> <ul style="list-style-type: none"> ○ White ● Matt Black ● Rose Gold ● Champagne ● Dark Silver 	5	2 824 82A	<p>1-gang - unswitched, with USB charger Type-C - 18 W</p> <p>Fast charge feature: Power Delivery</p> <ul style="list-style-type: none"> ○ White ● Matt Black ● Rose Gold ● Champagne ● Dark Silver
8	2 824 86-C		5	2 824 82A-C	
8	2 824 86-C1		5	2 824 82A-C1	
8	2 824 86-C2		5	2 824 82A-C2	
8	2 824 86-C3		5	2 824 82A-C3	
8	2 824 80	<p>1-gang single pole - switched - with LED power indicator</p> <ul style="list-style-type: none"> ○ White ● Matt Black ● Rose Gold ● Champagne ● Dark Silver 	5	2 824 83A	<p>1-gang single pole - switched, with USB charger Type-C - 18 W</p> <p>Fast charge feature: Power Delivery</p> <ul style="list-style-type: none"> ○ White ● Matt Black ● Rose Gold ● Champagne ● Dark Silver
8	2 824 80-C		5	2 824 83A-C	
8	2 824 80-C1		5	2 824 83A-C1	
8	2 824 80-C2		5	2 824 83A-C2	
8	2 824 80-C3		5	2 824 83A-C3	
5	2 824 31	<p>2-gang - unswitched</p> <ul style="list-style-type: none"> ○ White ● Matt Black ● Rose Gold ● Champagne ● Dark Silver 	5	2 824 43	<p>2-gang single pole - switched, with USB chargers Type-A and Type-C - 3 A - 5 V_{DC} - 15 W</p> <ul style="list-style-type: none"> ○ White ● Matt Black ● Rose Gold ● Champagne ● Dark Silver
5	2 824 31-C		5	2 824 43-C	
5	2 824 31-C1		5	2 824 43-C1	
5	2 824 31-C2		5	2 824 43-C2	
5	2 824 31-C3		5	2 824 43-C3	
5	2 824 33	<p>2-gang single pole - switched</p> <ul style="list-style-type: none"> ○ White ● Matt Black ● Rose Gold ● Champagne ● Dark Silver 	5	2 823 36	<p>2-gang single pole - switched, with USB chargers Type-A and Type-C - 27 W</p> <p>Fast charge feature: Power Delivery</p> <ul style="list-style-type: none"> ○ White ● Matt Black ● Rose Gold ● Champagne ● Dark Silver
5	2 824 33-C		5	2 823 36-C	
5	2 824 33-C1		5	2 823 36-C1	
5	2 824 33-C2		5	2 823 36-C2	
5	2 824 33-C3		5	2 823 36-C3	
5	2 824 87	<p>2-gang double pole - switched</p> <ul style="list-style-type: none"> ○ White ● Matt Black ● Rose Gold ● Champagne ● Dark Silver 	5	2 823 36	<p>British Standard socket outlets 15 A - 250 V~</p> <p>Conform to BS 546</p> <p>1-gang single pole - switched</p> <ul style="list-style-type: none"> ○ White ● Matt Black ● Rose Gold ● Champagne ● Dark Silver
5	2 824 87-C		8	2 824 37	
5	2 824 87-C1		8	2 824 37-C	
5	2 824 87-C2		8	2 824 37-C1	
5	2 824 87-C3		8	2 824 37-C2	
5	2 824 81	<p>2-gang single pole - switched - with LED power indicator</p> <ul style="list-style-type: none"> ○ White ● Matt Black ● Rose Gold ● Champagne ● Dark Silver 	8	2 824 37-C3	
5	2 824 81-C				
5	2 824 81-C1				
5	2 824 81-C2				
5	2 824 81-C3				