

Galion™

socket outlets, fused connection units and cable outlets



2 824 36



2 824 34-C1



2 824 85A



2 824 53



2 824 52-C1

Material: Polycarbonate front cover plates
 Dimensions: 86 x 88 mm (1-gang) / 146 x 88 mm (2-gang)
 Supplied with 2 screws M 3.5 for BS boxes. Supplied complete with plate
 All sockets integrate child protection

Pack	Cat.Nos	British Standard socket outlets 5 A - 250 V~
8	2 824 38	Conform to BS 546 1-gang single pole - switched <ul style="list-style-type: none"> ○ White ● Matt Black ● Rose Gold ● Champagne ● Dark Silver
8	2 824 38-C	
8	2 824 38-C1	
8	2 824 38-C2	
8	2 824 38-C3	
8	2 824 36	EURO-US standard socket outlet 16 A - 250 V~ 2P+E - 2-gang <ul style="list-style-type: none"> ○ White ● Matt Black ● Rose Gold ● Champagne ● Dark Silver
8	2 824 36-C	
8	2 824 36-C1	
8	2 824 36-C2	
8	2 824 36-C3	
8	2 824 34	Multistandard socket outlets 16 A - 250 V~ 1-gang - switched <ul style="list-style-type: none"> ○ White ● Matt Black ● Rose Gold ● Champagne ● Dark Silver
8	2 824 34-C	
8	2 824 34-C1	
8	2 824 34-C2	
8	2 824 34-C3	
5	2 824 35	2-gang - switched <ul style="list-style-type: none"> ○ White ● Matt Black ● Rose Gold ● Champagne ● Dark Silver
5	2 824 35-C	
5	2 824 35-C1	
5	2 824 35-C2	
5	2 824 35-C3	
5	2 824 42A	Multistandard socket outlets 16 A - 250 V~ - with USB chargers Consumption in passive mode < 0.08 W 1-gang - switched, with USB charger Type-A - 3 A - 5 V~ - 15 W <ul style="list-style-type: none"> ○ White ● Matt Black ● Rose Gold ● Champagne ● Dark Silver
5	2 824 42A-C	
5	2 824 42A-C1	
5	2 824 42A-C2	
5	2 824 42A-C3	
5	2 824 85A	1-gang - switched, with USB charger Type-C - 18 W Fast charge feature: Power Delivery <ul style="list-style-type: none"> ○ White ● Matt Black ● Rose Gold ● Champagne ● Dark Silver
5	2 824 85A-C	
5	2 824 85A-C1	
5	2 824 85A-C2	
5	2 824 85A-C3	

Pack	Cat.Nos	Multistandard socket outlets 16 A - 250 V~ - with USB chargers (continued)
5	2 824 44	2 gang single pole - switched, with USB chargers Type-A and Type-C - 3 A - 5 V~ - 15 W <ul style="list-style-type: none"> ○ White ● Matt Black ● Rose Gold ● Champagne ● Dark Silver
5	2 824 44-C	
5	2 824 44-C1	
5	2 824 44-C2	
5	2 824 44-C3	
5	2 823 37	2 gang single pole - switched, with USB chargers Type-A and Type-C - 27 W Fast charge feature: Power Delivery <ul style="list-style-type: none"> ○ White ● Matt Black ● Rose Gold ● Champagne ● Dark Silver
5	2 823 37-C	
5	2 823 37-C1	
5	2 823 37-C2	
5	2 823 37-C3	
8	2 824 50	Fused connection units - 13 A Conform to BS 1363 part 4 1-gang <ul style="list-style-type: none"> ○ White ● Matt Black ● Rose Gold ● Champagne ● Dark Silver
8	2 824 50-C	
8	2 824 50-C1	
8	2 824 50-C2	
8	2 824 50-C3	
8	2 824 51	1-gang - with switch <ul style="list-style-type: none"> ○ White ● Matt Black ● Rose Gold ● Champagne ● Dark Silver
8	2 824 51-C	
8	2 824 51-C1	
8	2 824 51-C2	
8	2 824 51-C3	
8	2 824 53	1-gang - with switch + LED power indicator <ul style="list-style-type: none"> ○ White ● Matt Black ● Rose Gold ● Champagne ● Dark Silver
8	2 824 53-C	
8	2 824 53-C1	
8	2 824 53-C2	
8	2 824 53-C3	
8	2 824 54	Cable outlets 1-gang - 45 A <ul style="list-style-type: none"> ○ White ● Matt Black ● Rose Gold ● Champagne ● Dark Silver
8	2 824 54-C	
8	2 824 54-C1	
8	2 824 54-C2	
8	2 824 54-C3	
8	2 824 52	1-gang - 20 A <ul style="list-style-type: none"> ○ White ● Matt Black ● Rose Gold ● Champagne ● Dark Silver
8	2 824 52-C	
8	2 824 52-C1	
8	2 824 52-C2	
8	2 824 52-C3	