



2 824 57-C



2 824 49-C2














2 824 63-C1



2 824 47

Material: Polycarbonate front cover plates
 Dimensions: 86 x 88 mm
 Supplied with 2 screws M 3.5 for BS boxes. Supplied complete with plate

Pack	Cat.Nos	Television sockets	Pack	Cat.Nos	Double USB Type-A chargers
8	2 824 57	Single TV socket, Female  <ul style="list-style-type: none"> ○ White ● Matt Black ● Rose Gold ● Champagne ● Dark Silver 	5	2 824 47	3 A - 5 V _{DC} - 15 W Consumption in passive mode < 0.08 W  <ul style="list-style-type: none"> ○ White ● Matt Black ● Rose Gold ● Champagne ● Dark Silver
8	2 824 57-C		5	2 824 47-C	
8	2 824 57-C1		5	2 824 47-C1	
8	2 824 57-C2		5	2 824 47-C2	
8	2 824 57-C3		5	2 824 47-C3	
8	2 824 49	Single TV sockets "F" type with screws, star attenuation < 1dB SAT: 0 - 2400 MHz  <ul style="list-style-type: none"> ○ White ● Matt Black ● Rose Gold ● Champagne ● Dark Silver 	8	2 824 48	USB and HDMI data sockets  <ul style="list-style-type: none"> ○ White ● Matt Black ● Rose Gold ● Champagne ● Dark Silver
8	2 824 49-C		8	2 824 48-C	
8	2 824 49-C1		8	2 824 48-C1	
8	2 824 49-C2		8	2 824 48-C2	
8	2 824 49-C3		8	2 824 48-C3	
8	2 824 59	TV-R-SAT sockets Low attenuation: 1.5 dB  <ul style="list-style-type: none"> ○ White ● Matt Black ● Rose Gold ● Champagne ● Dark Silver 			
8	2 824 59-C				
8	2 824 59-C1				
8	2 824 59-C2				
8	2 824 59-C3				
Telephone sockets					
8	2 824 45	RJ 11 socket  <ul style="list-style-type: none"> ○ White ● Matt Black ● Rose Gold ● Champagne ● Dark Silver 			
8	2 824 45-C				
8	2 824 45-C1				
8	2 824 45-C2				
8	2 824 45-C3				
8	2 824 46	Double RJ 11 socket  <ul style="list-style-type: none"> ○ White ● Matt Black ● Rose Gold ● Champagne ● Dark Silver 			
8	2 824 46-C				
8	2 824 46-C1				
8	2 824 46-C2				
8	2 824 46-C3				
Data sockets					
8	2 824 60	RJ 45 cat. 5e UTP  <ul style="list-style-type: none"> ○ White ● Matt Black ● Rose Gold ● Champagne ● Dark Silver 			
8	2 824 60-C				
8	2 824 60-C1				
8	2 824 60-C2				
8	2 824 60-C3				
8	2 824 62	Double RJ 45 cat. 5e UTP  <ul style="list-style-type: none"> ○ White ● Matt Black ● Rose Gold ● Champagne ● Dark Silver 			
8	2 824 62-C				
8	2 824 62-C1				
8	2 824 62-C2				
8	2 824 62-C3				
8	2 824 61	RJ 45 cat. 6 UTP  <ul style="list-style-type: none"> ○ White ● Matt Black ● Rose Gold ● Champagne ● Dark Silver 			
8	2 824 61-C				
8	2 824 61-C1				
8	2 824 61-C2				
8	2 824 61-C3				
8	2 824 63	Double RJ 45 cat. 6 UTP  <ul style="list-style-type: none"> ○ White ● Matt Black ● Rose Gold ● Champagne ● Dark Silver 			
8	2 824 63-C				
8	2 824 63-C1				
8	2 824 63-C2				
8	2 824 63-C3				