

Mallia™ Senses

data sockets



Mallia™ Senses

television sockets



2 811 59MB



2 811 65BA

Dimensions: 86 x 86 mm
Compact mechanism for greater wiring space
Supplied with 2 screws M 3.5 for BS boxes
Supplied as complete product with protective film



2 811 57DB

Conform to EN 50083-2 and European directive
Dimensions: 86 x 86 mm
Supplied with 2 screws M 3.5 for BS boxes
Supplied as complete product with protective film

Pack	Cat.Nos	Data sockets
		Compliant with ISO/IEC 11 801, EN 50173 and ANSI/TIA 568 standards
		RJ 45 cat. 5e UTP
5	2 811 61BA	Brushed Aluminium
5	2 811 61BB	● Brushed Black
5	2 811 61CH	● Champagne
5	2 811 61DB	● Dark Bronze
5	2 811 61DS	● Dark Silver
5	2 811 61MB	● Matt Black
5	2 811 61MW	○ Matt White
		RJ 45 cat. 6 UTP
5	2 811 62BA	Brushed Aluminium
5	2 811 62BB	● Brushed Black
5	2 811 62CH	● Champagne
5	2 811 62DB	● Dark Bronze
5	2 811 62DS	● Dark Silver
5	2 811 62MB	● Matt Black
5	2 811 62MW	○ Matt White
		RJ 45 cat. 6 STP
5	2 811 59BA	Brushed Aluminium
5	2 811 59BB	● Brushed Black
5	2 811 59CH	● Champagne
5	2 811 59DB	● Dark Bronze
5	2 811 59DS	● Dark Silver
5	2 811 59MB	● Matt Black
5	2 811 59MW	○ Matt White
		Double RJ 45 cat. 5e UTP
5	2 811 64BA	Brushed Aluminium
5	2 811 64BB	● Brushed Black
5	2 811 64CH	● Champagne
5	2 811 64DB	● Dark Bronze
5	2 811 64DS	● Dark Silver
5	2 811 64MB	● Matt Black
5	2 811 64MW	○ Matt White
		Double RJ 45 cat. 6 UTP
5	2 811 65BA	Brushed Aluminium
5	2 811 65BB	● Brushed Black
5	2 811 65CH	● Champagne
5	2 811 65DB	● Dark Bronze
5	2 811 65DS	● Dark Silver
5	2 811 65MB	● Matt Black
5	2 811 65MW	○ Matt White
		Double RJ 45 cat. 6 STP
5	2 811 58BA	Brushed Aluminium
5	2 811 58BB	● Brushed Black
5	2 811 58CH	● Champagne
5	2 811 58DB	● Dark Bronze
5	2 811 58DS	● Dark Silver
5	2 811 58MB	● Matt Black
5	2 811 58MW	○ Matt White

Pack	Cat.Nos	Multiple entries television sockets
		For DVBT, cable cast and satellite installation (with individual demodulator) DVBT HDTV compatible TV: male connector (Ø9.5 mm) R: female connector (Ø9.5 mm) SAT: "F" type connector Recommended coaxial cable 17 VATC
		TV-R-SAT sockets - star attenuation < 1.5 dB
		TV: 5-68/120-862 MHz R: 87.5-108 MHz FM / 174-223 MHz DAB+ SAT: 550-2400 MHz Installation recommended in flush-mounting box depth 40 mm
5	2 811 57BA	Brushed Aluminium
5	2 811 57BB	● Brushed Black
5	2 811 57CH	● Champagne
5	2 811 57DB	● Dark Bronze
5	2 811 57DS	● Dark Silver
5	2 811 57MB	● Matt Black
5	2 811 57MW	○ Matt White
		TV-SAT sockets - star attenuation < 1.5 dB
		TV: 5-68/120-862 MHz. SAT: 950-2400 MHz Installation recommended in flush-mounting box depth 40 mm
5	2 811 53BA	Brushed Aluminium
5	2 811 53BB	● Brushed Black
5	2 811 53CH	● Champagne
5	2 811 53DB	● Dark Bronze
5	2 811 53DS	● Dark Silver
5	2 811 53MB	● Matt Black
5	2 811 53MW	○ Matt White