



2 811 34AMW



2 811 30ABA



2 811 36DB



2 811 37DS

Dimensions: 86 x 86 mm (1-gang) / 146 x 86 mm (2-gang)
 Supplied with 2 screws M 3.5 for BS boxes
 Supplied as complete product with protective film
 All sockets integrate child protection

Pack	Cat.Nos
1	2 811 34ABA
1	2 811 34ABB
1	2 811 34ACH
1	2 811 34ADB
1	2 811 34ADS
1	2 811 34AMB
1	2 811 34AMW
1	2 811 30ABA
1	2 811 30ABB
1	2 811 30ACH
1	2 811 30ADB
1	2 811 30ADS
1	2 811 30AMB
1	2 811 30AMW
1	2 811 33ABA
1	2 811 33ABB
1	2 811 33ACH
1	2 811 33ADB
1	2 811 33ADS
1	2 811 33AMB
1	2 811 33AMW
1	2 811 31ABA
1	2 811 31ABB
1	2 811 31ACH
1	2 811 31ADB
1	2 811 31ADS
1	2 811 31AMB
1	2 811 31AMW
1	2 811 36BA
1	2 811 36BB
1	2 811 36CH
1	2 811 36DB
1	2 811 36DS
1	2 811 36MB
1	2 811 36MW

British standard socket outlets - 13 A - 250 V~ with USB charger
 Conform to BS 1363-2
 USB charger conform to BS EN 62368-1
 Consumption in passive mode < 0.08 W

1-gang single pole switched with USB Type-A - 3 A - 5 V_{DC} - 15 W

- Brushed Aluminium
- Brushed Black
- Champagne
- Dark Bronze
- Dark Silver
- Matt Black
- Matt White

1-gang single pole switched with USB Type-C - 18 W
 Fast charge feature: Power Delivery

- Brushed Aluminium
- Brushed Black
- Champagne
- Dark Bronze
- Dark Silver
- Matt Black
- Matt White

1-gang single pole unswitched with USB Type-A - 3 A - 5 V_{DC} - 15 W

- Brushed Aluminium
- Brushed Black
- Champagne
- Dark Bronze
- Dark Silver
- Matt Black
- Matt White

1-gang single pole unswitched with USB Type-C - 18 W
 Fast charge feature: Power Delivery

- Brushed Aluminium
- Brushed Black
- Champagne
- Dark Bronze
- Dark Silver
- Matt Black
- Matt White

2-gang single pole switched with USB Type-A + Type-C - 3 A - 5 V_{DC} - 15 W
 Consumption in passive mode < 0.08 W

- Brushed Aluminium
- Brushed Black
- Champagne
- Dark Bronze
- Dark Silver
- Matt Black
- Matt White

Pack	Cat.Nos
1	2 811 37BA
1	2 811 37BB
1	2 811 37CH
1	2 811 37DB
1	2 811 37DS
1	2 811 37MB
1	2 811 37MW
5	2 811 28BA
5	2 811 28BB
5	2 811 28CH
5	2 811 28DB
5	2 811 28DS
5	2 811 28MB
10	2 811 28MW
5	2 811 29BA
5	2 811 29BB
5	2 811 29CH
5	2 811 29DB
5	2 811 29DS
5	2 811 29MB
10	2 811 29MW
5	2 811 32BA
5	2 811 32BB
5	2 811 32CH
5	2 811 32DB
5	2 811 32DS
5	2 811 32MB
10	2 811 32MW

British standard socket outlets - 13 A - 250 V~ with USB charger (continued)
2-gang single pole switched with USB Type-A + Type-C - 27 W
 Fast charge feature: Power Delivery
 Consumption in passive mode: < 0.07 W

- Brushed Aluminium
- Brushed Black
- Champagne
- Dark Bronze
- Dark Silver
- Matt Black
- Matt White

British standard socket outlets 15 A - 250 V~
 Conform to BS 546

1-gang - switched

- Brushed Aluminium
- Brushed Black
- Champagne
- Dark Bronze
- Dark Silver
- Matt Black
- Matt White

1-gang - switched with red LED power indicator

- Brushed Aluminium
- Brushed Black
- Champagne
- Dark Bronze
- Dark Silver
- Matt Black
- Matt White

British standard socket outlets 5 A - 250 V~
 Conform to BS 546

1-gang - switched

- Brushed Aluminium
- Brushed Black
- Champagne
- Dark Bronze
- Dark Silver
- Matt Black
- Matt White