

# Mallia™ Senses

multistandard socket outlets and cable outlets



2 811 25ADS



2 811 23BB



2 811 38DS



2 811 47MB

Dimensions: 86 x 86 mm (1-gang) / 146 x 86 mm (2-gang)  
 Supplied with 2 screws M 3.5 for BS boxes  
 Supplied as complete product with protective film  
 All sockets integrate child protection

Pack	Cat.Nos	Multistandard switched socket outlets - 16 A - 250 V $\sim$ / 15 A - 127 V $\sim$
		<b>1-gang 2P+E</b>
5	2 811 20BA	<ul style="list-style-type: none"> <li>● Brushed Aluminium</li> <li>● Brushed Black</li> <li>● Champagne</li> <li>● Dark Bronze</li> <li>● Dark Silver</li> <li>● Matt Black</li> <li>○ Matt White</li> </ul>
5	2 811 20BB	
5	2 811 20CH	
5	2 811 20DB	
5	2 811 20DS	
5	2 811 20MB	
10	2 811 20MW	
		<b>2-gang 2P+E</b>
5	2 811 22BA	<ul style="list-style-type: none"> <li>● Brushed Aluminium</li> <li>● Brushed Black</li> <li>● Champagne</li> <li>● Dark Bronze</li> <li>● Dark Silver</li> <li>● Matt Black</li> <li>○ Matt White</li> </ul>
5	2 811 22BB	
5	2 811 22CH	
5	2 811 22DB	
5	2 811 22DS	
5	2 811 22MB	
10	2 811 22MW	
		<b>Multistandard socket outlets 16 A - 250 V<math>\sim</math> / 15 A - 127 V<math>\sim</math> with USB charger</b>
		USB charger conform to IEC 62368-1
		<b>1-gang 2P+E switched + USB Type-A - 3 A - 5 V<math>\sim</math> - 15 W</b>
		Consumption in passive mode < 0.08 W
1	2 811 21ABA	<ul style="list-style-type: none"> <li>● Brushed Aluminium</li> <li>● Brushed Black</li> <li>● Champagne</li> <li>● Dark Bronze</li> <li>● Dark Silver</li> <li>● Matt Black</li> <li>○ Matt White</li> </ul>
1	2 811 21ABB	
1	2 811 21ACH	
1	2 811 21ADB	
1	2 811 21ADS	
1	2 811 21AMB	
1	2 811 21AMW	
		<b>1-gang 2P+E switched + USB Type-C - 18 W</b>
		Fast charge feature: Power Delivery Consumption in passive mode < 0.08 W
1	2 811 25ABA	<ul style="list-style-type: none"> <li>● Brushed Aluminium</li> <li>● Brushed Black</li> <li>● Champagne</li> <li>● Dark Bronze</li> <li>● Dark Silver</li> <li>● Matt Black</li> <li>○ Matt White</li> </ul>
1	2 811 25ABB	
1	2 811 25ACH	
1	2 811 25ADB	
1	2 811 25ADS	
1	2 811 25AMB	
1	2 811 25AMW	
		<b>2-gang 2x2P+E switched + USB Type-A + Type-C - 3 A - 5 V<math>\sim</math> - 15 W</b>
		Consumption in passive mode < 0.08 W
1	2 811 23BA	<ul style="list-style-type: none"> <li>● Brushed Aluminium</li> <li>● Brushed Black</li> <li>● Champagne</li> <li>● Dark Bronze</li> <li>● Dark Silver</li> <li>● Matt Black</li> <li>○ Matt White</li> </ul>
1	2 811 23BB	
1	2 811 23CH	
1	2 811 23DB	
1	2 811 23DS	
1	2 811 23MB	
1	2 811 23MW	

Pack	Cat.Nos	Multistandard socket outlets 16 A - 250 V $\sim$ / 15 A - 127 V $\sim$ with USB charger (continued)
		<b>2-gang 2x2P+E switched + USB Type-A + Type-C - 27 W</b>
		Fast charge feature: Power Delivery Consumption in passive mode: < 0.07 W
1	2 811 38BA	<ul style="list-style-type: none"> <li>● Brushed Aluminium</li> <li>● Brushed Black</li> <li>● Champagne</li> <li>● Dark Bronze</li> <li>● Dark Silver</li> <li>● Matt Black</li> <li>○ Matt White</li> </ul>
1	2 811 38BB	
1	2 811 38CH	
1	2 811 38DB	
1	2 811 38DS	
1	2 811 38MB	
1	2 811 38MW	
		<b>Cable outlets</b>
		<b>20 A</b>
10	2 811 47BA	<ul style="list-style-type: none"> <li>● Brushed Aluminium</li> <li>● Brushed Black</li> <li>● Champagne</li> <li>● Dark Bronze</li> <li>● Dark Silver</li> <li>● Matt Black</li> <li>○ Matt White</li> </ul>
10	2 811 47BB	
10	2 811 47CH	
10	2 811 47DB	
10	2 811 47DS	
10	2 811 47MB	
10	2 811 47MW	
5	2 811 48CH	<ul style="list-style-type: none"> <li>● Champagne</li> <li>● Dark Bronze</li> <li>● Dark Silver</li> <li>● Matt Black</li> <li>○ Matt White</li> </ul>
5	2 811 48DB	
5	2 811 48DS	
5	2 811 48MB	
5	2 811 48MW	