

Mallia™ Senses

Euro-US and German standards socket outlets



Mallia™ Senses

fused connection units and USB charger



2 811 04DB



2 811 26DS

Dimensions: 86 x 86 mm
Supplied with 2 screws M 3.5 for BS boxes
Supplied as complete product with protective film
All sockets integrate child protection

Euro-US standard socket outlets

Pack	Cat.Nos	
		16 A - 250 V~
		1-gang 2P+E
5	2 811 03BA	● Brushed Aluminium
5	2 811 03BB	● Brushed Black
5	2 811 03CH	● Champagne
5	2 811 03DB	● Dark Bronze
5	2 811 03DS	● Dark Silver
5	2 811 03MB	● Matt Black
10	2 811 03MW	○ Matt White
		1-gang duplex 2P+E
5	2 811 04BA	● Brushed Aluminium
5	2 811 04BB	● Brushed Black
5	2 811 04CH	● Champagne
5	2 811 04DB	● Dark Bronze
5	2 811 04DS	● Dark Silver
5	2 811 04MB	● Matt Black
10	2 811 04MW	○ Matt White
		1-gang duplex switched 2P
5	2 811 24BA	● Brushed Aluminium
5	2 811 24BB	● Brushed Black
5	2 811 24CH	● Champagne
5	2 811 24DB	● Dark Bronze
5	2 811 24DS	● Dark Silver
5	2 811 24MB	● Matt Black
10	2 811 24MW	○ Matt White
		Euro-US standard socket outlets - 16 A - 250 V~ with USB charger
		USB charger conform to IEC 62368-1
		1-gang duplex single pole + USB Type-A + Type-C - 3.1 A - 5 V_{DC} - 15 W
		Consumption in passive mode < 0.08 W
1	2 812 04BA	● Brushed Aluminium
1	2 812 04BB	● Brushed Black
1	2 812 04CH	● Champagne
1	2 812 04DB	● Dark Bronze
1	2 812 04DS	● Dark Silver
1	2 812 04MB	● Matt Black
1	2 812 04MW	○ Matt White
		German standard socket outlets - 16 A - 250 V~
		Conform to IEC 60884-1
		1-gang 2P+E
5	2 811 26BA	● Brushed Aluminium
5	2 811 26BB	● Brushed Black
5	2 811 26CH	● Champagne
5	2 811 26DB	● Dark Bronze
5	2 811 26DS	● Dark Silver
5	2 811 26MB	● Matt Black
10	2 811 26MW	○ Matt White



2 811 40MW



2 811 42MB



2 812 10BA

Dimensions: 86 x 86 mm
Supplied with 2 screws M 3.5 for BS boxes
Supplied as complete product with protective film

13 A fused connection units

Pack	Cat.Nos	
		Conform to BS 1363- 4
		Unswitched
5	2 811 40BA	● Brushed Aluminium
5	2 811 40BB	● Brushed Black
5	2 811 40CH	● Champagne
5	2 811 40DB	● Dark Bronze
5	2 811 40DS	● Dark Silver
5	2 811 40MB	● Matt Black
10	2 811 40MW	○ Matt White
		Unswitched with red LED power indicator
5	2 811 49BA	● Brushed Aluminium
5	2 811 49BB	● Brushed Black
5	2 811 49CH	● Champagne
5	2 811 49DB	● Dark Bronze
5	2 811 49DS	● Dark Silver
5	2 811 49MB	● Matt Black
10	2 811 49MW	○ Matt White
		Switched
5	2 811 41BA	● Brushed Aluminium
5	2 811 41BB	● Brushed Black
5	2 811 41CH	● Champagne
5	2 811 41DB	● Dark Bronze
5	2 811 41DS	● Dark Silver
5	2 811 41MB	● Matt Black
10	2 811 41MW	○ Matt White
		Switched with red LED power indicator
5	2 811 42BA	● Brushed Aluminium
5	2 811 42BB	● Brushed Black
5	2 811 42CH	● Champagne
5	2 811 42DB	● Dark Bronze
5	2 811 42DS	● Dark Silver
5	2 811 42MB	● Matt Black
10	2 811 42MW	○ Matt White
		USB Type-C chargers
		Used for charging the battery of a portable device : smartphones, tablet or laptop 30 W power on single USB port (for laptop charging), 24 W power shared on two ports (for two smartphones charging) Consumption in passive mode < 0.1 W Conform to IEC 62884-2011-01 Supplied without cord
		Double USB sockets 2 x Type-C - 30 W
		Fast charge feature: Power Delivery
1	2 812 10BA	● Brushed Aluminium
1	2 812 10BB	● Brushed Black
1	2 812 10CH	● Champagne
1	2 812 10DB	● Dark Bronze
1	2 812 10DS	● Dark Silver
1	2 812 10MB	● Matt Black
1	2 812 10MW	○ Matt White