

Mallia™ Senses with Netatmo

connected micromodule switches



Step 2: Connected products



Home + Control



5 742 43

Used to create your connected installation, require prior installation of a gateway pack for connected installation
Conform to IEC 60669-2-5

Pack	Cat.Nos	Connected micromodule switches with neutral
1	5 742 43	<p>Used to connect lights with a ceiling box installation Can be controlled by one or more wireless light switches and/or mechanical push-buttons Zigbee Certified Product</p> <p>ON/OFF switch 100 W LED, wired Compatible with all loads: - LEDs and CFL lamps: 100 W LED - Incandescent and halogen lamps: 300 W - ELV halogen and CFL lamps with separate ballast: 250 VA</p> <p>Switch with dimmer option, 150 W LED, wired For local or remote ON/OFF / dimming control of lighting Dimmer mode can be activated from the Home + Control App. Memory level function</p>
1	0 648 99	<p>Compatible with all loads: - Dimmable LEDs and CFL lamps: 150 W LED - Incandescent and halogen lamps: 150 W - ELV halogen and CFL lamps with separate ballast: 150 VA</p>

Mallia™ Senses with Netatmo

connected light switches with dimmer option



Step 2: Connected products



Home + Control



2 815 09MB

Used to create your connected installation, require prior installation of a gateway pack for connected installation
Conform to IEC 60669-2-5

Pack	Cat.Nos	Connected light switches with dimmer option
		<p>Compact mechanism for greater wiring space Supplied with 2 screws M3,5 for BS boxes Supplied as complete product with the protection film Dim.: 86 x 86 mm For local or remote ON/OFF or dimming control of lighting Can be controlled by one or more connected wireless light switches or mechanical push-buttons without lamps Memory level function Can be installed in place of an existing switch in a flush-mounting box depth 25 mm Dimmer mode and locator/indicator function can be activated from the Home + Control App. Zigbee Certified Products</p> <p>With neutral, 150 W LED, 1-gang Compatible with all loads: - Dimmable LEDs and CFL lamps: 150 W LED - Incandescent and halogen lamps: 150 W - ELV halogen and CFL lamps with separate ballast: 150 VA</p>
1	2 815 08DS	<ul style="list-style-type: none"> ● Dark Silver ● Matt Black ○ Matt White
1	2 815 08MB	
1	2 815 08MW	
		<p>Without neutral, 5-125 W LED, 1-gang Compatible with all loads: - Dimmable LEDs and CFL lamps: 125 W LED - Incandescent and halogen lamps: 125 W - ELV halogen and CFL lamps with separate ballast: 125 VA Supplied with a bleeder</p>
1	2 815 09DS	<ul style="list-style-type: none"> ● Dark Silver ● Matt Black ○ Matt White
1	2 815 09MB	
1	2 815 09MW	