

# Mallia™ Senses with Netatmo

wireless light switches



## Step 2: Connected products



Home + Control






2 815 12MW



2 815 14DS

Used to create your connected installation, require prior installation of a gateway pack for connected installation  
Conform to IEC 60669-2-5

Pack	Cat.Nos	Wireless light switches
1	2 815 12DS 2 815 12MB 2 815 12MW	<p>Used to add an extra lighting control Easy pairing by tapping the connected wired product or by using the Home + Control App. Supplied with CR2032 3 V long-life battery for power supply Supplied with 2 removable stickers for fixing the control unit on any substrate LED function for low battery indication Supplied as complete product with the protection film Dim.: 86 x 86 mm Zigbee Certified Product</p> <p><b>1-gang</b> Controls up to 20 wired products: switches with or without dimmer option, micromodules, socket outlets</p>  <ul style="list-style-type: none"> <li>● Dark Silver</li> <li>● Matt Black</li> <li>○ Matt White</li> </ul>
1	2 815 13DS 2 815 13MB 2 815 13MW	<p><b>2-gang</b> Controls up to 2 x 20 wired products: switches with or without dimmer option, micromodules, socket outlets</p>  <ul style="list-style-type: none"> <li>● Dark Silver</li> <li>● Matt Black</li> <li>○ Matt White</li> </ul>
1	2 815 14DS 2 815 14MB 2 815 14MW	<p><b>3-gang</b> Controls up to 3 x 20 wired products: switches with or without dimmer option, micromodules, socket outlets</p>  <ul style="list-style-type: none"> <li>● Dark Silver</li> <li>● Matt Black</li> <li>○ Matt White</li> </ul>

# Mallia™ Senses with Netatmo

wireless lighting, curtain/roller blind controls



## Step 2: Connected products



Home + Control



0 648 75






0 676 94



2 815 18MW

Used to create your connected installation, require prior installation of a gateway pack for connected installation  
Conform to IEC 60669-2-5

Pack	Cat.Nos	Wireless motion sensor IP 44
1	0 648 75	 <p>Allows to control up to 20 wired switches, micromodules and socket outlets Easy pairing by tapping the connected wired products or by using the Home + Control App. Supplied with 2 x AA batteries For indoor and outdoor use Recommended distance between 2 sensors: 6 m Recommended installation height: 2.5 m Time delay adjustable from 15 s to 15 min Range: 8 m Detection angle: 140° Sensor range adjustable from 2 m to 8 m With ON/OFF test buttons Light level threshold adjustable from 1 to 1000 lux Zigbee Certified Product</p>
1	0 676 94	<p><b>Wireless switch ON/OFF module</b></p>  <p>Allows to transform a mechanical 2-way switch or push-button into a wireless ON/OFF switch Small size for easy integration into the wall box To be paired with one connected switch, micromodule, socket outlet Supplied with CR2032 3V long-life battery for power supply Zigbee Certified Product</p>
1	2 815 18DS 2 815 18MB 2 815 18MW	<p><b>Wireless curtain/roller blind switches</b></p> <p>Used for remote control or centralization of up to 20 connected wired curtain/roller blind switches Pair by tapping the selected roller blind switch(es) or by using the Home + Control App. Supplied with CR2032 3 V long-life battery for power supply LED function for low battery indication Supplied with 2 removable stickers for fixing the control unit on any substrate Supplied as complete product with the protection film Dim.: 86 x 86 mm Zigbee Certified Product</p> <p><b>1-gang</b></p>  <ul style="list-style-type: none"> <li>● Dark Silver</li> <li>● Matt Black</li> <li>○ Matt White</li> </ul>