



AR-68101



AR-68203



AR-68305



AR-68404



AR-68122

Conform to IEC 60669-1
 Dimensions: 86 x 86 mm
 Supplied with 2 screws M 3.5 for BS boxes. Supplied complete with plate

Single pole switches - 10 AX - 250 V~

Pack	Cat.Nos	Single pole switches - 10 AX - 250 V~
1	AR-68101	1-gang 2-way switch ● Brushed steel ● Brushed gold ○ Satin white ● Matt black
1	AR-68201	
1	AR-68301	
1	AR-68401	
1	AR-68106	1-gang intermediate switch ● Brushed steel ● Brushed gold ○ Satin white ● Matt black
1	AR-68206	
1	AR-68306	
1	AR-68406	
1	AR-68102	2-gang 2-way switch ● Brushed steel ● Brushed gold ○ Satin white ● Matt black
1	AR-68202	
1	AR-68302	
1	AR-68402	
1	AR-68103	3-gang 2-way switch ● Brushed steel ● Brushed gold ○ Satin white ● Matt black
1	AR-68203	
1	AR-68303	
1	AR-68403	

Single pole switches - 20 AX - 250 V~

1	AR-68107	1-gang 2-way switch ● Brushed steel ● Brushed gold ○ Satin white ● Matt black
1	AR-68207	
1	AR-68307	
1	AR-68407	
1	AR-68108	2-gang 2-way switch ● Brushed steel ● Brushed gold ○ Satin white ● Matt black
1	AR-68208	
1	AR-68308	
1	AR-68408	
1	AR-68109	3-gang 2-way switch ● Brushed steel ● Brushed gold ○ Satin white ● Matt black
1	AR-68209	
1	AR-68309	
1	AR-68409	

Double pole switch - 45 A - 250 V~

1	AR-68105	1-gang 2-way switch Illuminated double pole two-way switch Supplied with 230 V LED indicator ● Brushed steel ● Brushed gold ○ Satin white ● Matt black
1	AR-68205	
1	AR-68305	
1	AR-68405	

Push-buttons - 10 A - 250 V~

1	AR-68110	1-gang ● Brushed steel ● Brushed gold ○ Satin white ● Matt black
1	AR-68210	
1	AR-68310	
1	AR-68410	
1	AR-68111	2-gang ● Brushed steel ● Brushed gold ○ Satin white ● Matt black
1	AR-68211	
1	AR-68311	
1	AR-68411	

Rotary dimmer without neutral - 2-wire

Pack	Cat.Nos	Rotary dimmer without neutral - 2-wire
1	AR-68104	Push ON/OFF rotary universal dimmer 5 W / 300 W - 100-240 V~ - 50/60 Hz For flush-mounting in backbox depth 40 mm min. Equipped with overvoltage and short-circuit protection Screw terminals For all types of lamps: - dimmable LEDs and CFL lamps: 5 to 75 W LED - halogen with ferromagnetic or electronic transformer: 5 to 300 VA - fluorescent tube - ballast: 5 to 300 VA - halogen and incandescent 230 V: 5 to 300 W When switched on, gradually (2 seconds) lights up at the level set before last switch-off
1	AR-68204	
1	AR-68304	
1	AR-68404	



- Brushed steel
- Brushed gold
- Satin white
- Matt black

British Standard socket outlets 13 A - 250 V~

		Conform to BS 1363-2
1	AR-68124	1-gang single pole switched ● Brushed steel ● Brushed gold ○ Satin white ● Matt black
1	AR-68224	
1	AR-68324	
1	AR-68424	
1	AR-68122	1-gang double pole switched ● Brushed steel ● Brushed gold ○ Satin white ● Matt black
1	AR-68222	
1	AR-68322	
1	AR-68422	
1	AR-68129	1-gang double pole switched with blue LED indicator ● Brushed steel ● Brushed gold ○ Satin white ● Matt black
1	AR-68229	
1	AR-68329	
1	AR-68429	
1	AR-68123	2-gang single pole switched ● Brushed steel ● Brushed gold ○ Satin white ● Matt black
1	AR-68223	
1	AR-68323	
1	AR-68423	
1	AR-68121	2-gang double pole switched ● Brushed steel ● Brushed gold ○ Satin white ● Matt black
1	AR-68221	
1	AR-68321	
1	AR-68421	
1	AR-68130	2-gang double pole switched with blue LED indicators ● Brushed steel ● Brushed gold ○ Satin white ● Matt black
1	AR-68230	
1	AR-68330	
1	AR-68430	



British Standard socket outlet 5 A - 250 V~

		Conform to BS 1363-2
1	AR-68125	1-gang - single pole switched ● Brushed steel ● Brushed gold ○ Satin white ● Matt black
1	AR-68225	
1	AR-68325	
1	AR-68425	

