

# Art d'Arnould | COLLECTION

socket outlets with USB charger, fused connection units, TV, telephone and data sockets and reading light - Epure



AR-68127



AR-68226



AR-68428



AR-68381

Dimensions: 86 x 86 mm (1-gang) / 86 x 146 mm (2-gang)  
Supplied with 2 screws M 3.5 for BS boxes. Supplied complete with plate

Pack	Cat.Nos	British Standard socket outlets 13 A - 250 V~ with USB charger
1	AR-68127	<p>Conform to BS 1363-2 USB charger conform to IEC 60 950-1 Consumption in passive mode: &lt; 0.08 W</p> <p><b>1-gang single pole switched</b> USB Type-A 2.4 A charger - 5 V - 12 W Standby consumption &lt; 0.08 W</p> <ul style="list-style-type: none"> <li>● Brushed steel</li> <li>● Brushed gold</li> <li>○ Satin white</li> <li>● Matt black</li> </ul>
1	AR-68227	
1	AR-68327	
1	AR-68427	
1	AR-68126	<p><b>2-gang single pole switched</b> USB Type-A + Type-C charger - 3 A - 5 V - 15 W Standby consumption &lt; 0.08 W</p> <ul style="list-style-type: none"> <li>● Brushed steel</li> <li>● Brushed gold</li> <li>○ Satin white</li> <li>● Matt black</li> </ul>
1	AR-68226	
1	AR-68326	
1	AR-68426	
1	AR-68153	<p><b>Cooker control unit</b> 13 A BS switched socket outlet with indicator and 45 A master switch</p> <ul style="list-style-type: none"> <li>● Brushed steel</li> <li>● Brushed gold</li> <li>○ Satin white</li> <li>● Matt black</li> </ul>
1	AR-68253	
1	AR-68353	
1	AR-68453	
1	AR-68151	<p><b>Fused connection units - 13 A</b> <b>With double pole switch and blue LED indicator</b></p> <ul style="list-style-type: none"> <li>● Brushed steel</li> <li>● Brushed gold</li> <li>○ Satin white</li> <li>● Matt black</li> </ul>
1	AR-68251	
1	AR-68351	
1	AR-68451	
1	AR-68152	<p><b>With cable outlet and double pole switch with blue LED indicator</b></p> <ul style="list-style-type: none"> <li>● Brushed steel</li> <li>● Brushed gold</li> <li>○ Satin white</li> <li>● Matt black</li> </ul>
1	AR-68252	
1	AR-68352	
1	AR-68452	
1	AR-68128	<p><b>USB Type-A charger</b> Double USB sockets 2 x Type-A - 5 V~ - 3 A - 15 W</p> <ul style="list-style-type: none"> <li>● Brushed steel</li> <li>● Brushed gold</li> <li>○ Satin white</li> <li>● Matt black</li> </ul>
1	AR-68228	
1	AR-68328	
1	AR-68428	

Pack	Cat.Nos	TV sockets
1	AR-68143	<p><b>Single male TV socket</b></p> <ul style="list-style-type: none"> <li>● Brushed steel</li> <li>● Brushed gold</li> <li>○ Satin white</li> <li>● Matt black</li> </ul>
1	AR-68243	
1	AR-68343	
1	AR-68443	
1	AR-68144	<p><b>Single TV socket, "F" type</b></p> <ul style="list-style-type: none"> <li>● Brushed steel</li> <li>● Brushed gold</li> <li>○ Satin white</li> <li>● Matt black</li> </ul>
1	AR-68244	
1	AR-68344	
1	AR-68444	
1	AR-68145	<p><b>TV-R-SAT socket - DAB+</b></p> <ul style="list-style-type: none"> <li>● Brushed steel</li> <li>● Brushed gold</li> <li>○ Satin white</li> <li>● Matt black</li> </ul>
1	AR-68245	
1	AR-68345	
1	AR-68445	
1	AR-68146	<p><b>Telephone sockets</b> <b>BS master telephone socket</b></p> <ul style="list-style-type: none"> <li>● Brushed steel</li> <li>● Brushed gold</li> <li>○ Satin white</li> <li>● Matt black</li> </ul>
1	AR-68246	
1	AR-68346	
1	AR-68446	
1	AR-68147	<p><b>BS secondary telephone socket</b></p> <ul style="list-style-type: none"> <li>● Brushed steel</li> <li>● Brushed gold</li> <li>○ Satin white</li> <li>● Matt black</li> </ul>
1	AR-68247	
1	AR-68347	
1	AR-68447	
1	AR-68141	<p><b>RJ 45 sockets</b> <b>RJ 45 cat. 6 UTP</b></p> <ul style="list-style-type: none"> <li>● Brushed steel</li> <li>● Brushed gold</li> <li>○ Satin white</li> <li>● Matt black</li> </ul>
1	AR-68241	
1	AR-68341	
1	AR-68441	
1	AR-68142	<p><b>Double RJ 45 cat. 6 UTP</b></p> <ul style="list-style-type: none"> <li>● Brushed steel</li> <li>● Brushed gold</li> <li>○ Satin white</li> <li>● Matt black</li> </ul>
1	AR-68242	
1	AR-68342	
1	AR-68442	
1	AR-68181	<p><b>Reading light</b> 1 W LED reading light equipped with a flexible cable (length 300 mm) so the head can swivel and a 10 A two-way switch for control Warm white (3000 K). For installation in the bedhead Provides directional lighting For installation in 1-gang flush-mounting box, depth 50 mm</p> <ul style="list-style-type: none"> <li>● Brushed steel</li> <li>● Brushed gold</li> <li>○ Satin white</li> <li>● Matt black</li> </ul>
1	AR-68281	
1	AR-68381	
1	AR-68481	
1	AR-68161	<p><b>Blanking plates</b> <b>1-gang</b></p> <ul style="list-style-type: none"> <li>● Brushed steel</li> <li>● Brushed gold</li> <li>○ Satin white</li> <li>● Matt black</li> </ul>
1	AR-68261	
1	AR-68361	
1	AR-68461	
1	AR-68162	<p><b>2-gang</b></p> <ul style="list-style-type: none"> <li>● Brushed steel</li> <li>● Brushed gold</li> <li>○ Satin white</li> <li>● Matt black</li> </ul>
1	AR-68262	
1	AR-68362	
1	AR-68462	