

Synergy™

British standard socket outlets - white (continued)



7 300 60



7 300 70



7 300 74



7 300 89



7 300 69

Front plates: white thermoset
Terminal screws captive and backed off ready for cabling - large angled terminal entries
Compact mechanism for maximised wiring space
Supplied with faceplate screw caps

Pack	Cat.Nos	Double pole socket outlets 13 A - 250 V~
		Conform to BS 1363: Part. 2 With safety shutter mechanism For flush-mounting, back box can be min. 25 mm deep ASTA licence
		Options available as standard with red "power on" LED indicator Red LED "power on" upgrade pack also available
10	7 300 60	Switched 1-gang Nominal plate dimensions: 86 x 86 mm
5	7 300 70	2-gang Nominal plate dimensions: 86 x 146 mm
		Switched with red LED power indicator LED invisible until activated
10	7 300 61	1-gang Nominal plate dimensions: 86 x 86 mm
5	7 300 71	2-gang Nominal plate dimensions: 86 x 146 mm
		Switched for standard and clean earth applications
10	7 300 64	1-gang Nominal plate dimensions: 86 x 86 mm
5	7 300 74	2-gang Nominal plate dimensions: 86 x 146 mm
		Switched with red rocker
10	7 301 62	1-gang Nominal plate dimensions: 86 x 86 mm
5	7 301 61	2-gang Nominal plate dimensions: 86 x 146 mm

Pack	Cat.Nos	Socket outlets 15 A - 250 V~
		Conform to BS 546 Patented 3 pin safety shutter mechanism For flush-mounting, back box to be min. 35 mm deep Nominal plate dimensions: 86 x 86 mm
10	7 300 88	1-gang - unswitched
10	7 300 89	1-gang - switched, single pole
		Socket outlets 15 A - 127 V~
		Standard terminal screws For flush-mounting, back box to be min. 35 mm deep
5	7 300 85	1-gang - unswitched Nominal plate dimensions: 86 x 86 mm
5	7 300 86	2-gang - unswitched Nominal plate dimensions: 86 x 146 mm
		Socket outlets 5 A - 250 V~
		Conform to BS 546 Patented 3 pin safety shutter mechanism For flush-mounting, back box to be min. 25 mm deep Nominal plate dimensions: 86 x 86 mm
10	7 300 68	1-gang - unswitched
10	7 300 69	1-gang - switched, single pole
		Socket outlet 2 A - 250 V~
		Conform to BS 546 For flush-mounting, back box to be min. 25 mm deep Nominal plate dimensions: 86 x 86 mm
10	7 300 59	1-gang - unswitched



British standard multi-outlet extensions **p. 826**



BS plugs **p. 825**

