

Synergy™

blanking plates, accessories and surface mounting boxes - white



7 300 96





7 301 58






7 364 06









7 364 11

Pack	Cat.Nos	Blanking plates
10	7 300 95	 1-gang Nominal plate dimensions: 86 x 86 mm
10	7 300 96	 2-gang Nominal plate dimensions: 86 x 146 mm

Accessories		
Electronic LED All relevant Synergy white functions are designed to accept the LED packs for fitting at time of installation or retrospectively by a qualified person Can be used with fluorescent light		
10	7 301 58	 Electronic LED locator pack green diodes: max. current 0.2 mA provides illumination for function (e.g. switch) location in low light
10	7 300 58	 Electronic LED power indicator pack red diodes: nominal current 2 mA provides indication of "power on" condition in such functions as sockets and control switches
10	7 300 53	Cord outlet  1-gang box Nominal plate dimensions: 86 x 86 mm

Fixing accessories		
Splash-proof cover Mainly for socket protection IP 55 with or without plug engaged Space inside : 86 x 86 mm External dimensions : 129,2 x 107,2 x 54,1 mm		
4	6 176 36	 ● Mist grey

Pack	Cat.Nos	Surface-mounting moulded boxes
10	7 364 03	 1-gang - 16 mm deep 86 x 86 mm
10	7 364 06	 1-gang - 35 mm deep 86 x 86 mm
10	7 364 07	 1-gang - 50 mm deep and cable grip 86 x 86 mm
5	7 364 10	 2-gang - 35 mm deep 86 x 146 mm
5	7 364 11	 2-gang, 50 mm deep and cable grip 86 x 146 mm
5	7 364 13	 2 x 1-gang, 35 mm deep 86 x 172 mm