

Synergy™

fan switch and double pole switches - Authentic



Slim front plate:
 BSS: Plates made of austenitic Stainless Steel - non-magnetic - grade 304 L
 PSS: Plates made of Stainless Steel + rust resistance
 GG: Plates made of Stainless Steel + rust resistance
 Terminal screws captive and backed off ready for cabling - large angled terminal entries
 Compact mechanism for maximum wiring space

Pack	Cat.Nos	3 pole fan switches 10 A - 250 V~
1	8 330 09	Conform to BS EN 60669-1: 2000 With integrated padlockable safety block in OFF position. Flush mounting back box: min. 25 mm deep Nominal plate dimensions: 86 x 86 mm  <ul style="list-style-type: none"> ● Brushed stainless steel ● Polished stainless steel ● Glossy gold
1	8 332 09	
1	8 334 09	

Double pole switches 20 A - 250 V~
 Conform to BS EN 60669-1
 For flush-mounting, back box to be min. 25 mm deep
 Use cord outlet accessory Cat.No 7 300 53 for external cord outlet
 Nominal plate dimensions: 86 x 86 mm

Pack	Cat.Nos	DP switches
1	8 330 10	 <ul style="list-style-type: none"> ● Brushed stainless steel ● Polished stainless steel ● Glossy gold
1	8 332 10	
1	8 334 10	
1	8 330 16	DP switches + cord outlet + blue LED power indicator  <ul style="list-style-type: none"> ● Brushed stainless steel ● Polished stainless steel ● Glossy gold
1	8 332 16	
1	8 334 16	
1	8 330 12	DP switches + blue LED power indicator  <ul style="list-style-type: none"> ● Brushed stainless steel ● Polished stainless steel ● Glossy gold
1	8 332 12	
1	8 334 12	

Double pole switches 45 A - 250 V~
 Conform to BS EN 60669-1
 For flush-mounting, back box to be min. 45 mm deep

Pack	Cat.Nos	1-gang switch
1	8 330 22	Nominal plate dimensions: 86 x 86 mm  <ul style="list-style-type: none"> ● Brushed stainless steel ● Polished stainless steel ● Glossy gold
1	8 332 22	
1	8 334 22	
1	8 330 23	1-gang switch + blue LED power indicator Nominal plate dimensions: 86 x 86 mm  <ul style="list-style-type: none"> ● Brushed stainless steel ● Polished stainless steel ● Glossy gold
1	8 332 23	
1	8 334 23	
1	8 330 21	1-gang switch + blue LED power indicator large plate Nominal plate dimensions: 146 x 86 mm  <ul style="list-style-type: none"> ● Brushed stainless steel ● Polished stainless steel ● Glossy gold
1	8 332 21	
1	8 334 21	

Synergy™

telephone, data sockets and television sockets - Authentic



Slim front plate:
 BSS: Plates made of austenitic Stainless Steel - non-magnetic - grade 304 L
 PSS: Plates made of Stainless Steel + rust resistance
 GG: Plates made of Stainless Steel + rust resistance
 Terminal screws captive and backed off ready for cabling - large angled terminal entries
 Compact mechanism for maximum wiring space

Telephone sockets
 For flush-mounting, back box to be min. 35 mm deep
 Nominal plate dimensions: 86 x 86 mm

Pack	Cat.Nos	UK master
1	8 330 50	 <ul style="list-style-type: none"> ● Brushed stainless steel ● Polished stainless steel ● Glossy gold
1	8 332 50	
1	8 334 50	
1	8 330 51	UK secondary  <ul style="list-style-type: none"> ● Brushed stainless steel ● Polished stainless steel ● Glossy gold
1	8 332 51	
1	8 334 51	
1	8 330 54	RJ 11/RJ 12 - single  <ul style="list-style-type: none"> ● Brushed stainless steel ● Polished stainless steel ● Glossy gold
1	8 332 54	
1	8 334 54	

Data sockets
 Rapid cable connection
 For flush-mounting, back box to be min. 35 mm deep
 Nominal plate dimensions: 86 x 86 mm

Pack	Cat.Nos	RJ 45 cat. 6 UTP - single
1	8 330 56	 <ul style="list-style-type: none"> ● Brushed stainless steel ● Polished stainless steel ● Glossy gold
1	8 332 56	
1	8 334 56	
1	8 330 57	RJ 45 cat. 6 UTP - twin  <ul style="list-style-type: none"> ● Brushed stainless steel ● Polished stainless steel ● Glossy gold
1	8 332 57	
1	8 334 57	

Television sockets
 For flush-mounting, back box to be min. 35 mm deep
 Screened
 Nominal plate dimensions: 86 x 86 mm

Pack	Cat.Nos	TV socket - single male
1	8 330 40	 <ul style="list-style-type: none"> ● Brushed stainless steel ● Polished stainless steel ● Glossy gold
1	8 332 40	
1	8 334 40	
1	8 330 41	SAT socket - single "F" type  <ul style="list-style-type: none"> ● Brushed stainless steel ● Polished stainless steel ● Glossy gold
1	8 332 41	
1	8 334 41	
1	8 330 43	TV-R-SAT socket - "F" type  <ul style="list-style-type: none"> ● Brushed stainless steel ● Polished stainless steel ● Glossy gold
1	8 332 43	
1	8 334 43	