



8 330 65



8 334 67



8 330 78A



8 330 73A



8 327 79

Slim front plate:

BSS: Plates made of austenitic Stainless Steel - non-magnetic - grade 304 L

PSS: Plates made of Stainless Steel + rust resistance

GG: Plates made of Stainless Steel + rust resistance

Terminal screws captive and backed off ready for cabling - large angled terminal entries. Compact mechanism for maximum wiring space

Pack	Cat.Nos	Socket outlets 13 A - 250 V~
		Conform to BS 1363: Part. 2 With safety shutter mechanismFor flush-mounting, back box to be min. 25 mm deep ASTA licence
		1-gang - unswitched Nominal plate dimensions: 86 x 86 mm
1	8 330 65	● Brushed stainless steel
1	8 332 65	● Polished stainless steel
1	8 334 65	● Glossy gold
		2-gang - unswitched Nominal plate dimensions: 86 x 146 mm
1	8 330 75	● Brushed stainless steel
1	8 332 75	● Polished stainless steel
1	8 334 75	● Glossy gold
		Single pole socket outlets 13 A - 250 V~ Conform to BS 1363: Part. 2 With safety shutter mechanism For flush-mounting, back box to be min. 25 mm deep ASTA licence
		1-gang - switched Nominal plate dimensions: 86 x 86 mm
1	8 330 66	● Brushed stainless steel
1	8 332 66	● Polished stainless steel
1	8 334 66	● Glossy gold
		1-gang - switched with blue LED power indicator Nominal plate dimensions: 86 x 86 mm
1	8 330 67	● Brushed stainless steel
1	8 332 67	● Polished stainless steel
1	8 334 67	● Glossy gold
		2-gang - switched Nominal plate dimensions: 86 x 146 mm
1	8 330 76	● Brushed stainless steel
1	8 332 76	● Polished stainless steel
1	8 334 76	● Glossy gold
		2-gang - switched with blue LED power indicator Nominal plate dimensions: 86 x 146 mm
1	8 330 77	● Brushed stainless steel
1	8 332 77	● Polished stainless steel
1	8 334 77	● Glossy gold

Pack	Cat.Nos	Single pole socket outlets 13 A - 250 V~ with USB charger
		Conform to BS 1363-2 USB charger conform to IEC 60950-1
		1-gang - switched - USB Type-A - 3 A - 5 V~ - 15 W Consumption in passive mode < 0.07 W
1	8 330 78A	● Brushed Stainless steel
1	8 332 78A	● Polished Stainless steel
1	8 334 78A	● Glossy gold
		1-gang - switched - USB Type-C - 18 W Fast charge feature: Power Delivery Consumption in passive mode < 0.07 W
1	8 330 73A	● Brushed Stainless steel
1	8 332 73A	● Polished Stainless steel
1	8 334 73A	● Glossy gold
		2-gang - switched - USB Type-A + Type-C - 3 A - 5 V~ - 15 W Consumption in passive mode < 0.07 W
1	8 330 79	● Brushed Stainless Steel
1	8 332 79	● Polished Stainless Steel
1	8 334 79	● Glossy Gold
		2-gang - switched - USB Type-A + Type-C - 27 W Fast charge feature: Power Delivery Consumption in passive mode < 0.07 W
1	8 329 79	● Brushed Stainless Steel
1	8 328 79	● Polished Stainless Steel
1	8 327 79	● Glossy Gold