

Synergy™

British standard socket outlets - Authentic (continued)



8 334 89



8 330 69



8 332 59



8 330 44

Slim front plate:

BSS: Plates made of austenitic Stainless Steel - non-magnetic - grade 304 L

PSS: Plates made of Stainless Steel + rust resistance

GG: Plates made of Stainless Steel + rust resistance

Terminal screws captive and backed off ready for cabling - large angled terminal entries

Compact mechanism for maximum wiring space

Pack	Cat.Nos	Double pole socket outlets 13 A - 250 V~	Pack	Cat.Nos	Socket outlets 15 A - 127 V~
		Conform to BS 1363: Part. 2 With safety shutter mechanism For flush-mounting, back box to be min. 25 mm deep ASTA licence			For flush-mounting, back box to be min. 35 mm deep
		1-gang - switched Nominal plate dimensions: 86 x 86 mm			1-gang Nominal plate dimensions: 86 x 86 mm
1	8 330 60	● Brushed stainless steel	1	8 330 99	● Brushed stainless steel
1	8 332 60	● Polished stainless steel	1	8 334 99	● Polished stainless steel
1	8 334 60	● Glossy gold	1	8 333 99	● Glossy gold
		1-gang - switched with blue LED power indicator Nominal plate dimensions: 86 x 86 mm			2-gang Nominal plate dimensions: 86 x 146 mm
1	8 330 61	● Brushed stainless steel	1	8 332 99	● Brushed stainless steel
1	8 332 61	● Polished stainless steel	1	8 331 99	● Polished stainless steel
1	8 334 61	● Glossy gold	1	8 335 99	● Glossy gold
		2-gang - switched Nominal plate dimensions: 86 x 146 mm			Socket outlets 5 A - 250 V~
1	8 330 70	● Brushed stainless steel			Conform to BS 546 Patented 3 pin safety shutter mechanism, For flush-mounting, back box to be min. 25 mm deep
1	8 332 70	● Polished stainless steel			1-gang - unswitched Nominal plate dimensions: 86 x 86 mm
1	8 334 70	● Glossy gold	1	8 330 68	● Brushed stainless steel
		2-gang - switched with blue LED power indicator Nominal plate dimensions: 86 x 146 mm	1	8 332 68	● Polished stainless steel
1	8 330 71	● Brushed stainless steel	1	8 334 68	● Glossy gold
1	8 332 71	● Polished stainless steel			1-gang - switched - single pole Nominal plate dimensions: 86 x 146 mm
1	8 334 71	● Glossy gold	1	8 330 69	● Brushed stainless steel
		2-gang - switched outboard for standard and clean earth applications Nominal plate dimensions: 86 x 146 mm	1	8 332 69	● Polished stainless steel
1	8 330 74	● Brushed stainless steel	1	8 334 69	● Glossy gold
1	8 332 74	● Polished stainless steel			Socket outlets 2 A - 250 V~
1	8 334 74	● Glossy gold			Conform to BS 546 For flush-mounting, back box to be min. 25 mm deep Nominal plate dimensions: 86 x 86 mm
		Socket outlets 15 A - 250 V~			1-gang - unswitched
		Conform to BS 546 Patented 3 pin safety shutter mechanism, For flush-mounting, back box to be min. 35 mm deep Nominal plate dimensions: 86 x 86 mm	1	8 330 59	● Brushed stainless steel
1	8 330 88	● Brushed stainless steel	1	8 332 59	● Polished stainless steel
1	8 332 88	● Polished stainless steel	1	8 334 59	● Glossy gold
1	8 334 88	● Glossy gold			Double USB sockets 2 x Type-A
		1-gang - switched - single pole			For flush-mounting, back box to be min. 40 mm deep Input voltage: 110 V/ 230 V Comply with IEC 62684 5 V (output) - 3000 mA Wiring with 1.5 mm ² and 2.5 mm ² (only live and neutral)
1	8 330 89	● Brushed stainless steel	1	8 330 44	● Brushed stainless steel
1	8 332 89	● Polished stainless steel	1	8 332 44	● Polished stainless steel
1	8 334 89	● Glossy gold	1	8 334 44	● Glossy gold