

## Synergy™ - cooker control units and fused connection units - Authentic



8 332 29



8 334 37









Slim front plate:

BSS: Plates made of austenitic Stainless Steel - non-magnetic - grade 304 L

PSS: Plates made of Stainless Steel + rust resistance

GG: Plates made of Stainless Steel + rust resistance

Terminal screws captive and backed off ready for cabling - large angled terminal entries. Compact mechanism for maximum wiring space

Pack	Cat.Nos	Cooker control units - 250 V~
		Conform to BS 4177: 1992 For flush-mounting, back box to be min. 47 mm deep Nominal plate dimensions: 86 x 146 mm
1	8 330 29	 <b>45 A DP switch + 13 A DP switched socket outlet with blue LED power indicator</b> ● Brushed stainless steel ● Polished stainless steel ● Glossy gold
1	8 332 29	
1	8 334 29	
		<b>Fused connection units 13 A - 250 V~</b>
		Conform to BS 1363: Part. 4 Front cable outlet with cord grip Fuse supplied Locked captive fuse carrier (padlockable) For flush-mounting, back box to be min. 25 mm deep
		<b>Unswitched with cord outlet</b> Nominal plate dimensions: 86 x 86 mm
1	8 330 32	 ● Brushed stainless steel ● Polished stainless steel ● Glossy gold
1	8 332 32	
1	8 334 32	
		<b>Unswitched without cord outlet</b> Nominal plate dimensions: 86 x 86 mm
1	8 330 30	 ● Brushed stainless steel ● Polished stainless steel ● Glossy gold
1	8 332 30	
1	8 334 30	
		<b>Unswitched with blue LED power indicator</b> Nominal plate dimensions: 86 x 86 mm
1	8 330 31	 ● Brushed stainless steel ● Polished stainless steel ● Glossy gold
1	8 332 31	
1	8 334 31	
		<b>Unswitched with blue LED power indicator + cord outlet</b> Nominal plate dimensions: 86 x 86 mm
1	8 330 33	 ● Brushed stainless steel ● Polished stainless steel ● Glossy gold
1	8 332 33	
1	8 334 33	
		<b>DP switched without cord outlet</b> Nominal plate dimensions: 86 x 86 mm
1	8 330 34	 ● Brushed stainless steel ● Polished stainless steel ● Glossy gold
1	8 332 34	
1	8 334 34	
		<b>DP switched with blue LED power indicator</b> Nominal plate dimensions: 86 x 86 mm
1	8 330 35	 ● Brushed stainless steel ● Polished stainless steel ● Glossy gold
1	8 332 35	
1	8 334 35	
		<b>DP switched with blue LED power indicator + cord outlet</b> Nominal plate dimensions: 86 x 86 mm
1	8 330 37	 ● Brushed stainless steel ● Polished stainless steel ● Glossy gold
1	8 332 37	
1	8 334 37	

## Synergy™ - shaver sockets, cable outlets, blanking plates and cord outlets - Authentic



8 332 90



8 330 19



8 334 95







Slim front plates:

BSS: Plates made of austenitic Stainless Steel - non-magnetic - grade 304 L

PSS: Plates made of Stainless Steel + rust resistance

GG: Plates made of Stainless Steel + rust resistance

Terminal screws captive and backed off ready for cabling - large angled terminal entries. Compact mechanism for maximum wiring space

Pack	Cat.Nos	Shaver sockets
		Conform to BS EN 61558-2-5 Suitable for use with European, British and Australian 2 pin plugs Rating: 20 VA IP 24 Screwless live and neutral terminals For flush-mounting, back box to be min. 45 mm deep Nominal plate dimensions: 146 x 86 mm
		<b>230/120 V~ - 50/60 Hz</b>
1	8 330 90	 ● Brushed stainless steel ● Polished stainless steel ● Glossy gold
1	8 332 90	
1	8 334 90	
		<b>Cable outlets</b>
		Conform to BS 5733 Fitted clamp and outlet membrane With terminal block Nominal plate dimensions: 86 x 86 mm
		<b>20 A - 250 V~</b>
1	8 330 19	 ● Brushed stainless steel ● Polished stainless steel ● Glossy gold
1	8 332 19	
1	8 334 19	
		<b>45 A - 250 V~</b>
1	8 330 26	 ● Brushed stainless steel ● Polished stainless steel ● Glossy gold
1	8 332 26	
1	8 334 26	
		<b>Blanking plates</b>
		<b>1-gang</b> Nominal plate dimensions: 86 x 86 mm
1	8 330 95	 ● Brushed stainless steel ● Polished stainless steel ● Glossy gold
1	8 332 95	
1	8 334 95	
		<b>2-gang</b> Nominal plate dimensions: 86 x 146 mm
1	8 330 96	 ● Brushed stainless steel ● Polished stainless steel ● Glossy gold
1	8 332 96	
1	8 334 96	
		<b>Cord outlets</b>
		<b>1-gang</b> Nominal plate dimensions: 86 x 86 mm
1	8 330 52	 ● Brushed stainless steel ● Polished stainless steel ● Glossy gold
1	8 332 52	
1	8 334 52	