

Synergy™

British standard socket outlets and USB sockets - Sleek Design (continued)



8 324 78A



8 322 73A



8 320 79



8 320 44

Sleek design

BSS: Plates made of austenitic Stainless Steel - non-magnetic - grade 304 L

PSS: Plates made of Stainless Steel + rust resistance

GG: Plates made of Stainless Steel + rust resistance

Terminal screws captive and backed off ready for cabling - large angled terminal entries

Compact mechanism for maximum wiring space

Pack	Cat.Nos	Single pole socket outlets 13 A - 250 V \sim with USB charger
1	8 320 78A	<p>Conform to BS 1363-2 USB charger conform to IEC 60950-1</p> <p>1-gang - switched - USB Type-A - 3 A - 5 V\equiv - 15 W Consumption in passive mode < 0.07 W</p> <ul style="list-style-type: none"> ● Brushed Stainless Steel ● Polished Stainless Steel ● Glossy Gold
1	8 322 78A	
1	8 324 78A	
1	8 320 73A	<p>1-gang - switched - USB Type-C - 18 W Fast charge feature: Power Delivery Consumption in passive mode < 0.07 W</p> <ul style="list-style-type: none"> ● Brushed Stainless Steel ● Polished Stainless Steel ● Glossy Gold
1	8 322 73A	
1	8 324 73A	
1	8 320 79	<p>2-gang - switched - USB Type-A + Type-C - 3 A - 5 V\equiv - 15 W Consumption in passive mode < 0.07 W</p> <ul style="list-style-type: none"> ● Brushed Stainless Steel ● Polished Stainless Steel ● Glossy Gold
1	8 322 79	
1	8 324 79	
1	8 319 79	<p>2-gang - switched - USB Type-A + Type-C - 27 W Fast charge feature: Power Delivery Consumption in passive mode < 0.07 W</p> <ul style="list-style-type: none"> ● Brushed Stainless Steel ● Polished Stainless Steel ● Glossy Gold
1	8 318 79	
1	8 326 79	

Pack	Cat.Nos	Double pole socket outlets 13 A - 250 V \sim
1	8 320 60	<p>Conform to BS EN 1363: Part. 2 With safety shutter mechanism For flush-mounting, back box to be min. 35 mm deep Nominal plate dimensions: 86 x 86 mm (1-gang) 86 x 146 mm (2-gang) ASTA licence </p> <p>1-gang - switched</p> <ul style="list-style-type: none"> ● Brushed stainless steel ● Polished stainless steel ● Glossy gold
1	8 322 60	
1	8 324 60	
1	8 320 61	<p>1-gang - switched with blue LED power indicator</p> <ul style="list-style-type: none"> ● Brushed stainless steel ● Polished stainless steel ● Glossy gold
1	8 322 61	
1	8 324 61	

Pack	Cat.Nos	Double pole socket outlets 13 A - 250 V \sim (continued)
1	8 320 70	<p>2-gang - switched</p> <ul style="list-style-type: none"> ● Brushed stainless steel ● Polished stainless steel ● Glossy gold
1	8 322 70	
1	8 324 70	
1	8 320 71	<p>2-gang - switched with blue LED power indicator</p> <ul style="list-style-type: none"> ● Brushed stainless steel ● Polished stainless steel ● Glossy gold
1	8 322 71	
1	8 324 71	
1	8 320 89	<p>Socket outlets 15 A - 250 V\sim Conform to BS 546 Patented 3 pin safety shutter mechanism For flush-mounting, back box to be min. 35 mm deep Nominal plate dimensions: 86 x 86 mm</p> <p>1-gang - switched - single pole</p> <ul style="list-style-type: none"> ● Brushed stainless steel ● Polished stainless steel ● Glossy gold
1	8 322 89	
1	8 324 89	
1	8 320 69	<p>Socket outlets 5 A - 250 V\sim Conform to BS 546 Patented 3 pin safety shutter mechanism For flush-mounting, back box to be min. 25 mm deep Nominal plate dimensions: 86 x 86 mm</p> <p>1-gang - switched - single pole</p> <ul style="list-style-type: none"> ● Brushed stainless steel ● Polished stainless steel ● Glossy gold
1	8 322 69	
1	8 324 69	

Pack	Cat.Nos	Socket outlets 2 A - 250 V \sim
1	8 320 59	<p>Conform to BS 546 For flush-mounting, back box to be min. 25 mm deep Nominal plate dimensions: 86 x 86 mm</p> <p>1-gang - unswitched</p> <ul style="list-style-type: none"> ● Brushed stainless steel ● Polished stainless steel ● Glossy gold
1	8 322 59	
1	8 324 59	

Pack	Cat.Nos	Double USB sockets 2 x Type-A
1	8 320 44	<p>Conform to IEC 62684 For flush-mounting, back box to be min. 40 mm deep Input voltage: 110 V/ 230 V 5 V (output) - 3000 mA. Wiring with 1.5 mm² and 2.5 mm² (only live and neutral)</p> <ul style="list-style-type: none"> ● Brushed stainless steel ● Polished stainless steel ● Glossy gold
1	8 322 44	
1	8 324 44	