





7 646 46



7 645 89

Pack	Cat.Nos	Accessories
20	7 645 46	Cable outlets Allow multi-gang installation  ○ White ● Ivory
20	7 646 46	
20	7 645 45	Blanking plates  ○ White ● Ivory
20	7 646 45	
10	7 645 89	Mosaic adaptor ○ White Allows the integration of 2-module Mosaic Programme mechanisms such as buzzers, Wi-Power 1-gang station, skirting lights...










7 645 57



7 645 64

Mechanisms supplied with cover plates and support frames
To be equipped with plates (p. 749)
Fixing with screws or claws (supplied)
Installation in case of maintenance. An amplifier and a line balancing are recommended
TV: male connector (Ø9.5 mm)
R: female connector (Ø9.5 mm)
SAT: "F type" connector
Recommended coaxial cable: 17 VATC
Visual checking of the connection
TV: 5-68 / 120-862 MHz
R: 87.5-108 MHz
SAT: 950-2400 MHz

Pack	Cat.Nos	Passthrough sockets
10	7 645 52	Attenuation: -14 dB TV (male)  ○ White ● Ivory
10	7 646 52	
10	7 645 57	TV-SAT  ○ White ● Ivory
10	7 646 57	
10	7 645 64	TV-R-SAT  ○ White ● Ivory
10	7 646 64	

		Terminal sockets
		1 input with 1 resistance cap socket Attenuation: -10 dB
10	7 645 55	TV (male)  ○ White ● Ivory
10	7 646 55	
10	7 645 58	TV-SAT  ○ White ● Ivory
10	7 646 58	
10	7 645 65	TV-R-SAT  ○ White ● Ivory
10	7 646 65	
10	7 645 67	TV-R-SAT cover plate 33 mm fixing centers for local adaptation  ○ White ● Ivory
10	7 646 67	