



BT-KW4113



BT-KG4140A16F



BT-KM4141



BT-KM4126



BT-KW4188GFG6

Cover plates selection chart p. 756-757 and 758  
Plates selection chart p. 778

To be equipped with a support frame, a cover plate and a plate Shuttered for child safety

Pack	Cat.Nos	Italian standard socket outlets 10/16 A - 250 V~
10 10 10	BT-KW4113 BT-KG4113 BT-KM4113	<p>Conform to IEC 60884-1 and IEC 23-50 standards. 1 module. Can be equipped with a 2-module cover plate by associating the mechanism with 2 half-modules Cat.No BT-K4949 (p. 776)</p> <p><b>2P+E - 10 A</b></p> <ul style="list-style-type: none"> <li>○ White</li> <li>● Black</li> <li>● Sand</li> </ul> <p><b>2P+E - 16 A</b></p> <ul style="list-style-type: none"> <li>○ White</li> <li>● Black</li> <li>● Sand</li> </ul>
10 10 10	BT-KW4180 BT-KG4180 BT-KM4180	
10 10 10 10	BT-KW4140A16 BT-KG4140A16 BT-KM4140A16 BT-KR4140A16	<p><b>Italian/German standard socket outlets - 16 A - 250 V~</b></p> <p>Conform to IEC 60884-1 and VDE 620-1 standards. Suitable for Italian standard 2P, 2 P+E 10/16 A and 2P+E 16A socket outlets, and German standard 2P+E 16 A socket outlets</p> <p>2 modules. Can be equipped with a 3-module cover plate by associating the mechanism with 2 half-modules Cat.No BT-K4949 (p. 776)</p> <p><b>2P+E</b></p> <ul style="list-style-type: none"> <li>○ White</li> <li>● Black</li> <li>● Sand</li> <li>● Red</li> </ul> <p><b>2P+E - flat socket outlet</b></p> <p>When the plug is inserted, the socket surface slides inside the casing; it returns to its initial position when the plug is taken out</p> <ul style="list-style-type: none"> <li>○ White</li> <li>● Black</li> <li>● Sand</li> <li>● Red</li> </ul>
10 10 10 10	BT-KW4140A16F BT-KG4140A16F BT-KM4140A16F BT-KR4140A16	
10 10 10 10	BT-KW4141 BT-KG4141 BT-KM4141 BT-KR4141 BT-KV4141	<p><b>German standard socket outlet 16 A - 250 V~</b></p> <p>Conform to IEC 60884-1 and VDE 620-1 standards. 2 modules. Can be equipped with a 3-module cover plate by associating the mechanism with 2 half-modules Cat.No BT-K4949 (p. 776)</p> <p><b>2P+E</b></p> <ul style="list-style-type: none"> <li>○ White</li> <li>● Black</li> <li>● Sand</li> <li>● Red</li> <li>● Green</li> </ul>

Pack	Cat.Nos	Euro-US standard socket outlets 15/16 A - 127/250 V~
10 10 10	BT-KW4125 BT-KG4125 BT-KM4125	<p>Conform to IEC 60884-1 and NEMA WD-6 standards</p> <p><b>2P - 16 A</b></p> <p>2 modules. Can be equipped with a 3-module cover plate by associating the mechanism with 2 half-modules Cat.No BT-K4949 (p. 776)</p> <ul style="list-style-type: none"> <li>○ White</li> <li>● Black</li> <li>● Sand</li> </ul> <p><b>2P+E - 16 A</b></p> <p>2 modules. Can be equipped with a 3-module cover plate by associating the mechanism with 2 half-modules Cat.No BT-K4949 (p. 776)</p> <ul style="list-style-type: none"> <li>○ White</li> <li>● Black</li> <li>● Sand</li> </ul> <p><b>2P+E - 15 A</b></p> <p>2 modules. Can be equipped with a 3-module cover plate by associating the mechanism with 2 half-modules Cat.No BT-K4949 (p. 776)</p> <ul style="list-style-type: none"> <li>○ White</li> <li>● Black</li> <li>● Sand</li> </ul> <p><b>2 x 2P+E - 16 A</b></p> <p>3 modules</p> <ul style="list-style-type: none"> <li>○ White</li> <li>● Black</li> <li>● Sand</li> </ul> <p><b>2 x 2P+E - 15 A</b></p> <p>3 modules</p> <ul style="list-style-type: none"> <li>○ White</li> <li>● Black</li> <li>● Sand</li> </ul>
10 10 10	BT-KW4126 BT-KG4126 BT-KM4126	
10 10 10	BT-KW4129 BT-KG4129 BT-KM4129	
5 5 5	BT-KW4185 BT-KG4185 BT-KM4185	
5 5 5	BT-KW4188 BT-KG4188 BT-KM4188	
1 1 1	BT-KW4188GFG6 BT-KG4188GFG6 BT-KM4188GFG6	<p><b>American standard socket outlet 15 A - 127 V~</b></p> <p>Conform to IEC 60884-1 and NEMA WD-6 standards</p> <p><b>2P+E</b></p> <p>3 modules. Supplied with a support frame</p> <ul style="list-style-type: none"> <li>○ White</li> <li>● Black</li> <li>● Sand</li> </ul>