

Living Now

international socket outlets (continued)



BT-KW4126T



BT-K4139



BT-KW4183



BT-KW4164T13



BT-K4150



BT-K4132

Cover plates selection chart **p. 757 to 759**
Plates selection chart **p. 778**

To be equipped with a support frame, a cover plate and a plate
Shuttered for child safety

Pack	Cat.Nos	Thai standard socket outlets - 16 A 127/250 V~
10 10 10	BT-KW4126T BT-KG4126T BT-KM4126T	Conform to IEC 60884-1 and TIS 2162-2556 standards 2P+E 2 modules. Can be equipped with a 3-module cover plate by associating the mechanism with 2 half-modules Cat.No BT-K4949 (p. 776) ○ White ● Black ● Sand
5 5 5	BT-KW4185T BT-KG4185T BT-KM4185T	2 x 2P+E 3 modules ○ White ● Black ● Sand
10	BT-K4139	Multistandard socket outlet - 15 A 127 V~ 2P+E 2 modules Conform to IEC 60884-1 AS/FAR/AS Applicables standards
10 10 10	BT-KW4183 BT-KG4183 BT-KM4183	Israeli standard socket outlet 10/16 A - 250 V~ Conform to IEC 60884-1 and SI 32 part. 1.1 standards 2P+E 2 modules. Can be equipped with a 3-module cover plate by associating the mechanism with 2 half-modules Cat.No BT-K4949 (p. 776) ○ White ● Black ● Sand
10 10 10	BT-KW4164T13 BT-KG4164T13 BT-KM4164T13	Swiss standard socket outlets 10/16 A - 250 V~ Conform to IEC 60884-1 and SEV 1011 standards 2 modules 2P+E - 10 A ○ White ● Black ● Sand
10 10 10	BT-KW4164T23 BT-KG4164T23 BT-KM4164T23	2P+E - 16 A ○ White ● Black ● Sand

Pack	Cat.Nos	British standard socket outlet - 13 A 250 V~
10	BT-K4150	Conform to IEC 60884-1 and BS 1363-2 standards 2P+E 2 modules
10	BT-K4142A	French standard socket outlet - 16 A 250 V~ Conform to IEC 60884-1 and NFC 61-314 standards 2P+E 2 modules Can be equipped with a 3-module cover plate by associating the mechanism with 2 half-modules Cat.No BT-K4949 (p. 776)
10	BT-K4132	Australian standard socket outlets 10 A - 250 V~ Conform to IEC 60884-1 and ANZS 3112 standards 2P+E 2 modules
1	BT-K4134	2 x 2P+E 3 modules
10	BT-K4190N	Chinese standard socket outlets 10/16 A - 127/250 V~ Conform to IEC 60884-1 and GB 1002 standards 2P+E - 10 A 1 module
10	BT-K4189N	2P+E 2 modules 2P+E Chinese standard socket outlet + 2P 16 A Euro-US standard socket outlet
10	BT-K4181	2P+E - 16 A 2 modules