



BT-K4210M2D



BT-K4211M2C



BT-K4214M2D



BT-K4214D



BT-K4202D



BT-K4202F

Cover plates selection chart **p. 761-762**
Plates selection chart **p. 778**

To be equipped with a support frame, a cover plate and a plate
For DVB-T, Cablecast and satellite installation
UHD TV quality, 4GLTE compatible. For distribution of TV & Radio signals
Recommended coaxial cable: 17 VATC
TV: male connector (Ø9.5 mm) - 5-68/120-862 MHz
R: female connector (Ø9.5 mm) - 87.5 -108 MHz
SAT: F type connector - 950-2400 MHz
Conform to EN 50083 and EN 50083-2 European directive

Pack	Cat.Nos	Multi TV star sockets
1	BT-K4210M2D	TV-R-SAT socket - 2 modules Star demixed socket - DAB+ Low attenuation: 1.5 dB
1	BT-K4217M2D	TV-SAT sockets - 2 modules Star demixed socket Low attenuation: 1.5 dB
1	BT-K4217M2P14	Passthrough demixed socket Attenuation: 14 dB
1	BT-K4217M2P10	Terminal demixed socket Attenuation: 14 dB
1	BT-K4211M2C	TV-RD socket - 2 modules Double coaxial shunted socket for TV and FM-LMC reception For cable operator (Belgium: Telenet operator)
1	BT-K4214M2D	TV male socket + TV "F" type socket For single-user aerial systems 2 modules
1	BT-K4214D	TV "F" type socket 1 module

Pack	Cat.Nos	Single TV star sockets - 1 module
1	BT-K4202D	Can be equipped with a 2-module cover plate by associating the mechanism with 2 half-modules Cat.No BT-K4949 (p. 776) TV 9.5 mm male socket Low attenuation: 1.5 dB
1	BT-K4202F	TV "F" type socket Low attenuation: 1.5 dB
1	BT-K4202P14	Passthrough coaxial socket Low attenuation: 14 dB
1	BT-K4202P10	Terminal passthrough coaxial socket Low attenuation: 10 dB